

A-INSP-M40-68N-P-LG - Screw plug



1424522

<https://www.phoenixcontact.com/gb/products/1424522>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Screw plug, material for screw connection: PA, connecting thread: M40 x 1.5, color: lightgray RAL 7035



Commercial data

Item number	1424522
Packing unit	5 pc
Minimum order quantity	5 pc
Sales key	AF7DZX
Product key	AF7DZX
Catalog page	Page 702 (C-2-2019)
GTIN	4055626374277
Weight per piece (including packing)	13.34 g
Weight per piece (excluding packing)	13.33 g
Customs tariff number	39269097
Country of origin	DE

A-INSP-M40-68N-P-LG - Screw plug



1424522

<https://www.phoenixcontact.com/gb/products/1424522>

Technical data


Product properties

Product type	Plug for cable screw gland
Manufacturer	WISKA
Manufacturer Designation	EVSG-ORD 40

Connection data

Tightening torque	3 Nm
-------------------	------

Dimensions

Dimensional drawing	
Length	13 mm
Length of the connecting thread	8 mm
Diameter	40 mm
Connecting thread diameter	40 mm
Thread type connection side	M40 x 1.5
Thread pitch	1.5 mm

Material specifications

Material	PA
Seal material O-ring	EPDM
Material for screw connection	PA

Cable/line

Halogen-free	yes
--------------	-----

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP68
	IP66
Ambient temperature (operation)	-40 °C ... 100 °C

A-INSP-M40-68N-P-LG - Screw plug


1424522

<https://www.phoenixcontact.com/gb/products/1424522>



Drawings

Dimensional drawing



Dimensional drawing

A-INSP-M40-68N-P-LG - Screw plug



1424522

<https://www.phoenixcontact.com/gb/products/1424522>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1424522>



EAC

Approval ID: EAC-Zulassung

A-INSP-M40-68N-P-LG - Screw plug



1424522

<https://www.phoenixcontact.com/gb/products/1424522>

Classifications

ECLASS

ECLASS-13.0	23111190
-------------	----------

ETIM

ETIM 9.0	EC000032
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

A-INSP-M40-68N-P-LG - Screw plug



1424522

<https://www.phoenixcontact.com/gb/products/1424522>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk