

# CHARX T1HBI-DUST-COVER-SET - Protective cover



1305482

<https://www.phoenixcontact.com/in/products/1305482>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



CHARX connect universal, CCS type 1, Protective cover, Accessories, Plug-on assembly, housing: black, for vehicle charging inlet

## Product description

Protective cover

## Your advantages

- Developed and produced in accordance with the IATF 16949 automotive standard and ISO 9001
- Individual branding, thanks to the use your own logo
- Reliable protection of your socket outlet from weather and vandalism

## Commercial data

Item number	1305482
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	*****
Product key	XWCAFO
GTIN	4063151553142
Weight per piece (including packing)	95.1 g
Weight per piece (excluding packing)	91.8 g
Customs tariff number	39269097
Country of origin	PL

# CHARX T1HBI-DUST-COVER-SET - Protective cover



1305482

<https://www.phoenixcontact.com/in/products/1305482>

## Technical data

### Product properties

Product type	Cover
Product family	CHARX connect universal
Application	for vehicle charging inlet
Type	Accessories
Charging standard	CCS type 1

### Material specifications

Color (Housing)	black (9005)
Material (Housing)	Plastic

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection (Protective cap)	IP54
Ambient temperature (operation)	-30 °C ... 50 °C
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	5000 m (above sea level)

### Mounting

Mounting type Protective cap	Plug-on assembly
------------------------------	------------------

# CHARX T1HBI-DUST-COVER-SET - Protective cover



1305482

<https://www.phoenixcontact.com/in/products/1305482>

## Classifications

### ECLASS

ECLASS-11.0	27144792
ECLASS-12.0	27144792
ECLASS-13.0	27144792

### ETIM

ETIM 9.0	EC002884
----------	----------

### UNSPSC

UNSPSC 21.0	39121500
-------------	----------

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-10
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------