



**Part Number :** [393710005](#)

**Product Description :** 7.50mm Beau Eurostyle Pluggable Terminal Block, 180° Wire Entry, 5 Circuits

**Series Number :** 39371

**Status :** Active

**Product Category :** Terminal Blocks and Barrier Strip

**Engineering Number :** MX-CIF05003-0N



---

## Documents & Resources

### Drawings

[393710005\\_sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### [Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

### [Industry Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Terminal Blocks and Barrier Strip
Series	39371
Description	7.50mm Beau Eurostyle Pluggable Terminal Block, 180° Wire Entry, 5 Circuits
Application	Wire-to-Board
Component Type	Plug
Product Name	Eurostyle Pluggable
Type	PCB Terminal Blocks and Connectors
UPC	822348040193

### Agency

UL	E48521
----	--------

### Electrical

Current - Maximum per Contact	15.0A
Voltage - Maximum	300V

### Physical

Circuits (Loaded)	5
Circuits (maximum)	5
Color - Resin	Black

Entry Angle	180° Angle
Flammability	94V-0
Lock to Mating Part	None
Net Weight	11.470/g
Number of Rows	1
Orientation	N/A
Panel Mount	No
PCB Retention	N/A
Pitch - Mating Interface	7.50mm
Pitch - Termination Interface	7.50mm
Polarized to Mating Part	Yes
Stackable	Yes
Temperature Range - Operating	110°C
Wire Size (AWG)	12, 14, 16, 18, 20, 22, 24, 26, 28, 30
Wire Size mm <sup>2</sup>	0.05-2.50

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
7.50mm Beau Eurostyle Vertical PCB Headers	<u>39372</u>
7.50mm Beau Eurostyle Horizontal PCB Headers	<u>39373</u>