



HARD FERRITE

Flat magnets with threaded bush

- Shielded flat magnet made of hard ferrite with threaded bush
- Galvanised surface
- Temperature stability to **maximum 100°C**
- Use for clamping, assembling. Incorporation by screw fixing

Cat no Desc

E860RS	FERRITE POT M3 dia 10 × 4.5
E861RS	FERRITE POT M3 dia 13 × 4.5
E862RS	FERRITE POT M3 dia 16 × 4.5
E863RS	FERRITE POT M3 dia 20 × 6
E864RS	FERRITE POT M4 dia 25 × 7
E865RS	FERRITE POT M4 dia 32 × 7
E867RS	FERRITE POT M5 dia 40 × 8
E869RS	FERRITE POT M6 dia 50 × 10
E871RS	FERRITE POT M8 dia 63 × 14
E872RS	FERRITE POT M10 dia 80 × 18

RS 667-9996, 667-9977, 667-9970, 667-9974, 667-9983, 667-9986, 667-9980, 667-9999, 667-9992, 668-0028, 668-0021, 668-0025, 668-0034, 668-0015, 668-0019, 668-0009, 668-0003, 668-0012, 668-0006

MAGNET ASSEMBLIES


FOR CLAMPING, FIXING, ASSEMBLY

Flat magnets with / without threaded bush

- Shielded flat magnet with 3–5 times the clamping force of hard ferrite magnets
- Galvanised surface, magnetic core made of samarium cobalt (SmCo_3)
- Temperature stability to **maximum 200°C**
- Use for clamping, assembling. Incorporation by pressing / gluing in / casting compound

Cat no Desc

E760RS	SMCO SHALLOW POT dia 6 × 4.5
E761RS	SMCO SHALLOW POT dia 8 × 4.5
E762RS	SMCO SHALLOW POT dia 10 × 4.5
E763RS	SMCO SHALLOW POT dia 13 × 4.5
E764RS	SMCO SHALLOW POT dia 16 × 4.5
E765RS	SMCO SHALLOW POT dia 20 × 6
E766RS	SMCO SHALLOW POT dia 25 × 7
E767RS	SMCO SHALLOW POT dia 32 × 7
E770RS	SMCO POT MAGNET M3 dia 6 × 4.5
E771RS	SMCO POT MAGNET M3 dia 8 × 4.5
E772RS	SMCO POT MAGNET M3 dia 10 × 4.5
E773RS	SMCO POT MAGNET M3 dia 13 × 4.5
E774RS	SMCO POT MAGNET M4 dia 16 × 4.5
E775RS	SMCO POT MAGNET M4 dia 20 × 6
E776RS	SMCO POT MAGNET M4 dia 25 × 7
E777RS	SMCO POT MAGNET M5 dia 32 × 7



**SAMARIUM
COBALT**

Cylindrical magnets with toleranced dimensions

- Shouldered cylindrical magnets with 3–5 times the clamping force of hard ferrite magnets
- Fit tolerance to external diameter h 6w, magnetic core made of samarium cobalt (SmCo_3)
- Application: for clamping, assembling, incorporation by pressing in / gluing

Cat no Desc

E750RS	SMCO POT MAGNET H6 dia 6 × 20
E751RS	SMCO POT MAGNET H6 dia 8 × 20
E752RS	SMCO POT MAGNET H6 dia 10 × 20
E753RS	SMCO POT MAGNET H6 dia 13 × 20
E754RS	SMCO POT MAGNET H6 dia 16 × 20
E755RS	SMCO POT MAGNET H6 dia 20 × 25
E756RS	SMCO POT MAGNET H6 dia 25 × 35
E757RS	SMCO POT MAGNET H6 dia 32 × 40



**SAMARIUM
COBALT**