

HONEYWELL NORTH SHORT BRIM HARD HAT

Why Not Choose Both Quality and Price?

With enhanced performance, all-day comfort and durability – the Honeywell North Short Brim Hard Hat integrates the heritage of two renowned brands – Honeywell and North – into a new, cost-effective and certified head protection solution, with vented and non-vented versions.



Honeywell North Short Brim Hard Hat
SKU: NSB10001



Honeywell North Short Brim Hard Hat Vented
SKU: NSB11001

SET A NEW STANDARD FOR COMFORTABLE PROTECTION

In workplace environments such as industrial or construction sites, high rotations of personnel are common practice and providing dozens of workers with certified head protection can be expensive. Choosing a less known manufacturer, you might get a product with compromised quality that's not certified to the latest standards. That would put your workers' safety at risk and bring about possible customer service issues.

Honeywell has designed the North Short Brim Hard Hat to offer your workers certified quality protection, while also being cost-effective. Created by Honeywell, a recognized company known for its support, high performance and service, the North Short Brim Hard Hat provides quality protection, increased comfort and a competitive price.

QUALITY PROTECTION

Made of high-density polyethylene (HDPE), Honeywell North Short Brim Hard Hat is the quality safety solution for all-day wear, protecting against impact and falling or flying objects. If the hard hat isn't well-balanced or moves and slips out of place, it can increase risks and reduce worker productivity. Therefore, Honeywell has designed this hard hat with a four-point ratchet suspension, a dual-locking mechanism and an optional four-point chin strap to customize your fit according to your preferences and prevent the hard hat from getting loose. No matter if you work in extreme heat or cold environments, you'll benefit from the same reliable protection – the Honeywell North Hard Hat is resistant to temperatures from -22°F to 122°F (-30°C to +50°C).

INCREASED COMFORT

Benefit from increased comfort with Honeywell North Short Brim Hard Hat's light material – it is created to weigh up to 14.46 oz. (410 g), eliminating neck fatigue and increasing work productivity. Moreover, with an ergonomic design and several adjustment features, it provides an excellent fit for multiple head sizes. Choose between the vented hard hat for increased comfort and better cooling efficiency or the non-vented version to protect against electrical hazards.

COMPETITIVE PRICE


The Honeywell North Short Brim Hard Hat is the culmination of Honeywell's years of experience as a leading manufacturer of personal protective equipment (PPE), as well as extensive

market knowledge and engineering expertise. The Honeywell North Short Brim Hard Hat is the new generation of fully certified hard hats providing excellent protection, quality, comfort and a long lifespan, all for an affordable price. Compatible with Honeywell headgear accessories – face shields, welding and hearing protection – and certified to ANSI, CE/EN, CSA and NOM standards, the Honeywell North Short Brim Hard Hat delivers the quality protection you need for the price you expect.

Honeywell

FEATURES AND BENEFITS

FEATURE	DESCRIPTION
Protection	• Type I
Electrical class	• Non-vented version Class E (as per ANSI Z89.1-14) • Vented version Class C (as per ANSI Z89.1-14)
Material	• HDPE - High-density polyethylene
Ergonomic	• Fits multiple head sizes (6 ¹/₂ to 7 ⁷/₈ in - 52 to 63 cm - head circumference) • 4-point Ratchet suspension • Dual-locking mechanism prevents the hard hat to get loose in normal conditions • Optional four-point chin strap
Weight	• Up to 13.75 oz. (390 g) without the chin strap • Up to 14.46 oz. (410 g) with the chin strap
Ventilation	• Vented (NSB110) and non-vented (NSB100) options
High temperature resistance	• +50° C
Low temperature resistance	• -30° C
Compatibility	• +Compatible with the following Honeywell PPE adapters: - CP5005 plastic face-shield bracket - 3796VS1 helmet adapter for cap mounted earmuffs
Certifications	• ANSI (ANSI Z89.1 – 2014) standard • CE/EN (EN 397:2012 +A1:2012, EN 50365:2002 (non-vented versions) standard • CSA (CSA Z94.1-15) standard • NOM standard
Eight color options	• White • Yellow • Orange • Green • Gray • Black • Red • Dark blue
Industries	• Construction • Manufacturing • Mining • Oil and gas • Ship building • Traffic safety • Utilities



HONEYWELL NORTH SHORT BRIM HARD HAT



White
NSB10001



Yellow
NSB10002



Orange
NSB10003



Green
NSB10004



Gray
NSB10009



Black
NSB10011



Red
NSB10015



Dark Blue
NSB10071



Chin Strap
NSB100CS

HONEYWELL NORTH SHORT BRIM HARD HAT VENTED



White
NSB11001



Yellow
NSB11002



Orange
NSB11003



Green
NSB11004



Red
NSB11015



Dark Blue
NSB11071

ORDERING INFORMATION

SKU	DESCRIPTION	PACKAGING
HONEYWELL NORTH SHORT BRIM HARD HAT - UNVENTED		
NSB10001	Honeywell North Short Brim Hard Hat - White	20 Each Per Case, MOQ 500 Each
NSB10002	Honeywell North Short Brim Hard Hat - Yellow	20 Each Per Case, MOQ 500 Each
NSB10003	Honeywell North Short Brim Hard Hat - Orange	20 Each Per Case, MOQ 500 Each
NSB10004	Honeywell North Short Brim Hard Hat - Green	20 Each Per Case, MOQ 500 Each
NSB10009	Honeywell North Short Brim Hard Hat - Gray	20 Each Per Case, MOQ 500 Each
NSB10011	Honeywell North Short Brim Hard Hat - Black	20 Each Per Case, MOQ 500 Each
NSB10015	Honeywell North Short Brim Hard Hat - Red	20 Each Per Case, MOQ 500 Each
NSB10071	Honeywell North Short Brim Hard Hat - Dark Blue	20 Each Per Case, MOQ 500 Each
HONEYWELL NORTH SHORT BRIM HARD HAT - VENTED		
NSB11001	Honeywell North Short Brim Hard Hat - Vented - White	20 Each Per Case, MOQ 500 Each
NSB11002	Honeywell North Short Brim Hard Hat - Vented - Yellow	20 Each Per Case, MOQ 500 Each
NSB11003	Honeywell North Short Brim Hard Hat - Vented - Orange	20 Each Per Case, MOQ 500 Each
NSB11004	Honeywell North Short Brim Hard Hat - Vented - Green	20 Each Per Case, MOQ 500 Each
NSB11015	Honeywell North Short Brim Hard Hat - Vented - Red	20 Each Per Case, MOQ 500 Each
NSB11071	Honeywell North Short Brim Hard Hat - Vented - Dark Blue	20 Each Per Case, MOQ 500 Each
HONEYWELL NORTH SHORT BRIM HARD HAT - ACCESSORIES		
NSB100CS	Honeywell North Short Brim Hard Hat Chin Strap	20 Each Per Case, MOQ 500 Each
NSB100RS1	Honeywell North Short Brim Hard Hat Suspension	20 Each Per Case, MOQ 500 Each

For more information
www.sps.honeywell.com

**Honeywell Personal Protective Equipment
Malaysia (Asia Pacific Headquarters)**
Level 25, UOA Corporate Tower
Lobby B, The Vertical, Bangsar South City
59200 Kuala Lumpur, Malaysia
Tel: +603-2777 3948 / 3950
Email: hsp.asean@Honeywell.com

NORTH_HARD_HAT_DATASHEET_03/23
© 2023 Honeywell International Inc.

**THE
FUTURE
IS
WHAT
WE
MAKE IT**

Honeywell