



Cut

Ergonomic industrial gloves offering excellent cut protection, comfort and durability

- **Advanced defenses:** HyFlex® 72-285 hand protection gloves are made from Dyneema® to ensure excellent cut resistance
- **Improved durability:** These protective gloves are suitable for laundering up to 90°C, increasing their wear life
- **Enhanced ergonomics:** HyFlex® 72-285 work gloves feature an ergonomic design, which improves flexibility, dexterity and comfort
- **Food handling compliance:** These safety gloves are suitable for food contact and are available in three versions to better match the level of protection and dexterity required by specific applications



Industries

- Food Processing

Applications

- Assembly and disassembly of equipment
- Primary cutting

HyFlex[®]

ADVANCED MECHANICAL PROTECTION

72-285

Exceptional cut resistance, comfort and durability

Previously known as: Versatouch[®] 72-285

Key Features

- **Dyneema[®] material:** Superior cut resistance assured
- **Suitable for laundering up to 90°C:** Durable work gloves
- **Ergonomic design:** Improved wearer comfort

Technologies



DMF free



Performance Standards & Regulatory Compliance



EN388: 2016



1X4XB



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	PACKAGE
HyFlex [®] 72-285	Liner Material: Dyneema [®] , Polyester, Spandex		6, 7, 8, 9, 10	260-330 mm; 10.23-13.99 inches	3 pairs/bag, 2 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Ansell, [®] and [™] are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

Ansell