

## Connector assembly frame - HC-CIF-B10-HFFD-WH-AL - 1404221

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



HEAVYCON plug assembly frame, upper part for double locking latch, for HC-CIF...BFWD.. lower parts with double locking latch or for HC-CIF...BFFD.. lower parts, for type B10 contact inserts, with M4 screws with 3 mm Allen screw head, for NS35/7,5 DIN rails

### Why buy this product

- ✓ Sturdy metal version
- ✓ Open base, pre-assembled cable harnesses can be used
- ✓ Standardized design; both PE sheets for inserts are connected conductively
- ✓ Safe capacitive PE even when connected slightly askew



### Key commercial data

Packing unit	1 pc
GTIN	 4 046356 681933
Weight per Piece (excluding packing)	87.5 g
Custom tariff number	85389099
Country of origin	Poland

### Technical data

#### Dimensions

Length	103.2 mm
Width	56 mm

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

#### General

Type	For B10
Material	Cast aluminum, uncoated
Connection	For screw locking: M4, 3 mm Allen screw, 2 Nm tightening torque

## Connector assembly frame - HC-CIF-B10-HFFD-WH-AL - 1404221

### Classifications

#### eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209

#### ETIM

ETIM 3.0	EC002310
ETIM 4.0	EC002310
ETIM 5.0	EC002310

#### UNSPSC

UNSPSC 6.01	43172601
UNSPSC 7.0901	39121416
UNSPSC 11	43172601
UNSPSC 12.01	39121408
UNSPSC 13.2	39121408

### Approvals

#### Approvals

#### Approvals

#### EAC

#### Ex Approvals

#### Approvals submitted

#### Approval details

EAC
-----

### Accessories

#### Accessories

#### Device marking

## Connector assembly frame - HC-CIF-B10-HFFD-WH-AL - 1404221

### Accessories


Plastic label - US-EMLP (20X9) SR - 0828884



Plastic label, Card, silver, unlabeled, can be labeled with: THERMOMARK CARD, Mounting type: Adhesive, Lettering field: 20 x 9 mm

### Drawings

Dimensioned drawing



Dimensional drawing top view

Dimensioned drawing

