

FEATURES

- This RS PRO rackmount enclosure is made from high-grade cold-rolled steel, with the front and back panels made from lightweight aluminium
- Each unit offers top, base and side ventilation apertures for optimum cooling, especially when housing electronic equipment or components
- The two-layer front panel has been designed with an adjustable gap (0 – 20 mm)
- The whole enclosure unit is powder-coated following a 5-stage iron phosphate pre-treatment to prevent oxidisation and provide longer-lasting protection, especially in harsh environments
- The precise design and high-quality manufacturing standard enables fast and easy assembly while offering complete compatibility with all 19-inch standard equipment
- In addition to this, each unit has 2 extruded aluminium handles and 4 adhesive rubber feet for additional versatility across a wide range of applications
- Gloss black finish for easy cleaning and keeping the surface dust and debris free
- The enclosure unit and accessories supplied with the unit are packed flat for convenient shipment and storage
- Supplied with 4 fitted and 4 loose Board / Chassis plate / Component fixing crossbars
- The PF19 enclosure range is available in a wide variety of sizes
-

RS PRO Fitting Cases & Enclosures - Ventilated Rackmount Enclosure

RS Stock No.: 6657738



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO PF19 Series Rackmount Enclosure

Introducing the RS PRO PF19 Rackmount Enclosures, a high quality and heavy-duty electronic enclosure series, suitable for a wide range of uses. Constructed from a mixture of high grade rolled steel and lightweight aluminium panels, these rackmount enclosures offer a sturdy construction and combined with the tough powder-coated finish, provide long-lasting life of the product even in harsh environments. The enclosures are easy to use and assemble, thanks to the precision workmanship and well-engineered design. In addition to this, the high-quality materials that are used to manufacture this RS PRO enclosure offer a strong and aesthetically-pleasing finished product, suitable for a wide range of applications both at home or in industry.

General Specifications

| | |
|-------------------|--|
| Colour | Black |
| Ventilated | Yes |
| Rack Units | 6U |
| Features | The PF19 enclosure range is available in a wide variety of sizes |

Mechanical Specifications

| | |
|-------------------------------|-------------------|
| External Dimensions | 266 x 482 x 465mm |
| External Height | 266 mm |
| External Width | 482 mm |
| External Depth | 465mm |
| External Case Material | Aluminium, Steel |
| Front Panel Material | Aluminium |

Approvals

| | |
|---------------------|--------------------------------|
| Declarations | RoHS Certificate of Compliance |
|---------------------|--------------------------------|

Similar Products

| Stock No. | Brand | Product Name | External Case Material | Colour | Rack Units |
|-----------|--------|----------------------------|------------------------|-------------|------------|
| 6657674 | RS PRO | RS PRO, 3U Rack Mount Case | Aluminium, Steel | Natural | 3U |
| 6657677 | RS PRO | RS PRO, 3U Rack Mount Case | Aluminium, Steel | Black, Grey | 1U |

Dimension Drawings / Assembly Diagram / Accessories / Wiring Diagrams

Available Dimensions :

There are 24 different sizes and configurations which are available in :

- Height : 1.5U to 6U (B)
- Width : 482 (A)
- Depth : 90, 245, 335, 425 and 465 (D)

