

# Technical datasheet



171418282501

E1803518

FRAME 1-GANG WITH HINGED COVER BROWN MATT, INTEGRO FLOW

## Product Properties:

|                                    |               |
|------------------------------------|---------------|
| Anti-bacterial treatment           | No            |
| Surface finishing                  | Matt          |
| Mounting direction                 | Vertical      |
| Label space/information surface    | No            |
| With mounting grid                 | No            |
| Flush-mounted installation         | Yes           |
| Suitable for floor box             | No            |
| Suitable for built-in installation | Yes           |
| With hinged lid                    | Yes           |
| Transparent                        | No            |
| Type of fastening                  | Engage (snap) |
| RAL-number (similar)               | 8017 .        |
| Colour                             | Brown         |
| Surface protection                 | Untreated     |
| Material                           | Plastic       |
| Type of product                    | Ram           |
| Variant                            | N/A           |

## Dimensions:

|                                              |         |
|----------------------------------------------|---------|
| Number of units                              | 1 .     |
| Number of units horizontal                   | 1 .     |
| Number of units vertical                     | 1 .     |
| Number of modules horizontal (module system) | 1 .     |
| Number of modules vertical (module system)   | 1 .     |
| Number of switch inserts                     | 1 .     |
| Diameter bore hole (opening)                 | 42.5 mm |
| Depth                                        | 17.9 mm |
| Width                                        | 59.5 mm |
| Height                                       | 59.5 mm |
| MOQ                                          | 10 .    |
| Unit                                         | pcs     |

## Approvals:

## Compliance:

|                   |                                    |
|-------------------|------------------------------------|
| Conflict Minerals | N/A, Contains no conflict minerals |
| REACH             | No SVHC (Latest: 21 Jan 2025)      |
| RoHS              | RoHS 3 (2015/863)                  |
| SCIP              | Not Applicable                     |

## Other information:

|                    |                                                       |
|--------------------|-------------------------------------------------------|
| ETIM-Class         | EC000007 - Cover frame for domestic switching devices |
| ETIM-Release       | 9.0                                                   |
| Trademark          | Berker                                                |
| Product Group      | Integro Flow                                          |
| Search Description | 918282501                                             |
| Alternative SKU    | 171418282501                                          |
| E-no               | E1803518                                              |

## Logistic information:

|         |              |
|---------|--------------|
| Barcode | 401133423977 |
|---------|--------------|

|                   |                                                                      |
|-------------------|----------------------------------------------------------------------|
| Country of origin | DE                                                                   |
| E-no              | E1803518                                                             |
| Item status       | Stock item, normally in stock with reservation for in between sales. |
| MOQ               | 10 .                                                                 |
| Stock code        | 171418282501                                                         |
| Taric code        | 85389099                                                             |
| Unit              | pcs                                                                  |

\*We reserve the right to make technical changes and disclaim any typographical errors.