



DELTA i-system, titanium white, socket outlet 16 A 250 V, with grounding pin, 2-pole according to CEE 7, cover plate 55 x 55 mm

Model	
product brand name	DELTA
product designation	Socket outlet
design of the product	protective ground contact pin
cover version	central plate
design of the special power supply unit	without special current supply
design of the socket according to VDE 0620 for severe conditions	No
design of the phase tap	No
General technical data	
marking of socket outlet	without imprint
mounting type	fixing with claw and screw
surface processing	others
material	thermoplastic
Supply voltage	
operating voltage rated value	250 V
supply voltage frequency rated value	50 Hz
Protection class	
protection class IP	IP20
Main circuit	
operational current rated value	16 A
Appearance	
color	titanium white
Product details	
product component	
• ejection equipment	No
• labeling field	No
• increased touch protection	No
• residual current device	No
• miniature fuse	No
• integrated functional lighting	No
• integrated light source	No
• integrated orientation lighting	No
• hinged lid	No
product feature	
• lockable	No
• halogen-free	Yes
• transparent	No
Product function	
product function	

- socket selectable
- overvoltage protection

No
No

Number

number of units	1
number of sockets switchable	0

Connections

arrangement of contacts diagonal	No
type of electrical connection	plug terminal

Mechanical Design

height	70 mm
width	70 mm
depth	45 mm
fastening method	flush mounting
material of the enclosure	plastic

Environmental footprint

Environmental Product Declaration (EPD)	Yes
global warming potential [CO2 eq] total	4.77 kg
global warming potential [CO2 eq] during manufacturing	0.284 kg
global warming potential [CO2 eq] during operation	4.48 kg
global warming potential [CO2 eq] after end of life	7.42E-5 kg

Approvals Certificates

General Product Approval

other

Environment



[Confirmation](#)

[Miscellaneous](#)



Environment

[Environmental Confirmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5UB1350>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5UB1350>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5UB1350

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



