

## FEATURES

- AISI 304 Stainless Steel
- IP66 rating
- Fully wall mountable
- Lockable

# RS PRO Wall Boxes- 304 Stainless Steel Wall Box

RS Stock No.: 842-8383



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

## RS Pro IP66 Stainless Steel Wall Box

Brought to you by RS Pro, A range of stainless steel wall mounted enclosures. Enclosures are present in almost every industry and can store all manor of items, such as medical equipment or electronics. These boxes are rated at IP66 and provide an excellent degree of protection, whether it's used within an indoor or outdoor environment. With various sizes available, they are suitable for a wide selection of applications. All models are highly reliable and excellent quality.

### General Specifications

<b>Body Material</b>	<b>304 Stainless Steel</b>
<b>Number Of Doors</b>	<b>1</b>
<b>Colour</b>	<b>Unpainted</b>
<b>Gland Plate</b>	<b>No</b>
<b>Sealing Gasket</b>	<b>No</b>
<b>Door Lock Type</b>	<b>Single Lock System</b>
<b>Chassis Plate</b>	<b>Zinc-coated steel</b>
<b>Transparent Door</b>	<b>No</b>
<b>Fixing Kit</b>	<b>Yes</b>
<b>Application</b>	<b>Electrical</b>
<b>External Mounting Type</b>	<b>Bracket</b>
<b>Internal Mounting Type</b>	<b>Panel</b>
<b>Special Features</b>	<b>IK10 Against Mechanical Impacts</b>
<b>For Protection Of</b>	<b>Sensitive Electrical Equipment</b>

### Mechanical Specifications

<b>External Height</b>	<b>300 mm</b>
<b>External Width</b>	<b>200 mm</b>
<b>External Depth</b>	<b>400mm</b>
<b>Dimensions</b>	<b>300 x 200 x 400 mm</b>
<b>Thickness</b>	<b>1.2 mm for enclosure &amp; door</b>

### Protection Category

<b>IP Rating</b>	<b>IP66</b>
------------------	-------------

**Approvals**

Declarations	RoHS Certificate of Compliance
--------------	--------------------------------

**Similar Products**

Stock No.	Brand	Product Name	Colour	Body Material	Dimensions
775-5300	RS PRO	Steel Wall Box	Grey	Steel	300 mm x 250 mm x 150 mm
775-5788	RS PRO	Steel Wall Box	Grey	Steel	300 mm x 200 mm x 150 mm

Additional Information / Installation Diagrams / Illustrations / Accessories

