

## Insert label - MM-EMT (EX4)R C1 WH/BK - 1169312

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Insert label, Roll, white/black, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: insert, lettering field size: continuous x 3 mm

### Your advantages

- ✓ High-quality and solvent-resistant marking solution for industrial applications that is created by means of thermal transfer printing
- ✓ Insert label for the KMK marker carrier for cable marking
- ✓ Easy and efficient material cartridge system: Includes both the material to be printed and the corresponding ink ribbon
- ✓ No visible difference between retrospective marking and existing markings created with a desktop roll printer
- ✓ Thanks to the continuous format, only one material is required for all sleeve lengths
- ✓ Thanks to their special shape, insert labels remain securely inside the collar once inserted



### Key Commercial Data

Packing unit	1 pc
GTIN	 4 063151 187118
GTIN	4063151187118
Weight per Piece (excluding packing)	47.600 g
Custom tariff number	96121010
Country of origin	China
Sales Key	BG221E

### Technical data

#### Dimensions

Length (b)	5.5 m
Width (a)	8 mm

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.

## Insert label - MM-EMT (EX4)R C1 WH/BK - 1169312

### Technical data

#### General

Color	white/black
Components	free from silicone, halogen, and cadmium
Material	Polyester
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Marking mounting type	insert
Testing substances harmful to the wetting properties of lacquers (LABS conformity)	VW PV 3.10.7:2005-02
Result	Test passed
UV resistance	Following ISO 4892-2:2013-03
Result	Test passed
Test duration	96 h
Test for wipe resistance of inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Testing in a condensation changing climate in the presence of sulfur dioxide	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1,0 S
Cycles	2
Salt spray test	DIN EN 60068-2-11:2000-02
Result	Test passed

#### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

### Classifications

#### eCl@ss

eCl@ss 10.0.1	27400629
eCl@ss 11.0	27281106
eCl@ss 9.0	27400629

#### ETIM

ETIM 7.0	EC001288
----------	----------

### Accessories

#### Accessories

Marker carrier cable

## Insert label - MM-EMT (EX4)R C1 WH/BK - 1169312

### Accessories

#### Conductor marker carrier - PATG 0/10 - 1013795



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 0.6 ... 1.2 mm, lettering field size: 10 x 4 mm

---

#### Conductor marker carrier - PATG 0/12 - 0827076



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 0.6 ... 1.2 mm, lettering field size: 12 x 4 mm

---

#### Conductor marker carrier - PATG 0/15 - 1013740



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 0.6 ... 1.2 mm, lettering field size: 15 x 4 mm

---

#### Conductor marker carrier - PATG 0/18 - 0820507



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 0.6 ... 1.2 mm, lettering field size: 18 x 4 mm

---

#### Conductor marker carrier - PATG 0/23 - 0828046



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 0.6 ... 1.2 mm, lettering field size: 23 x 4 mm

---

## Insert label - MM-EMT (EX4)R C1 WH/BK - 1169312

### Accessories

#### Conductor marker carrier - PATG 1/10 - 1013805



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 1.5 ... 2.5 mm, lettering field size: 10 x 4 mm

---

#### Conductor marker carrier - PATG 1/12 - 0827077



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 1.5 ... 2.5 mm, lettering field size: 12 x 4 mm

---

#### Conductor marker carrier - PATG 1/15 - 1013025



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 1.5 ... 2.5 mm, lettering field size: 15 x 4 mm

---

#### Conductor marker carrier - PATG 1/18 - 0820510



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 1.5 ... 2.5 mm, lettering field size: 18 x 4 mm

---

#### Conductor marker carrier - PATG 1/23 - 1013847



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 1.5 ... 2.5 mm, lettering field size: 23 x 4 mm

---

## Insert label - MM-EMT (EX4)R C1 WH/BK - 1169312

### Accessories

Conductor marker carrier - PATG 1/30 - 0822440



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 1.5 ... 2.5 mm, lettering field size: 30 x 4 mm

---

Conductor marker carrier - PATG 2/10 - 1013818



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 2 ... 4 mm, lettering field size: 10 x 4 mm

---

Conductor marker carrier - PATG 2/12 - 0827078



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 2 ... 4 mm, lettering field size: 12 x 4 mm

---

Conductor marker carrier - PATG 2/15 - 1013038



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 2 ... 4 mm, lettering field size: 15 x 4 mm

---

Conductor marker carrier - PATG 2/18 - 0820523



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 2 ... 4 mm, lettering field size: 18 x 4 mm

---

## Insert label - MM-EMT (EX4)R C1 WH/BK - 1169312

### Accessories

Conductor marker carrier - PATG 2/23 - 1013850



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 2 ... 4 mm, lettering field size: 23 x 4 mm

---

Conductor marker carrier - PATG 2/30 - 0822453



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 2 ... 4 mm, lettering field size: 30 x 4 mm

---

Conductor marker carrier - PATG 3/10 - 1013821



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 4 ... 7 mm, lettering field size: 10 x 4 mm

---

Conductor marker carrier - PATG 3/12 - 0827079



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 4 ... 7 mm, lettering field size: 12 x 4 mm

---

Conductor marker carrier - PATG 3/15 - 1013041



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 4 ... 7 mm, lettering field size: 15 x 4 mm

---

## Insert label - MM-EMT (EX4)R C1 WH/BK - 1169312

### Accessories

Conductor marker carrier - PATG 3/18 - 0820536



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 4 ... 7 mm, lettering field size: 18 x 4 mm

---

Conductor marker carrier - PATG 3/23 - 1013863



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 4 ... 7 mm, lettering field size: 23 x 4 mm

---

Conductor marker carrier - PATG 3/30 - 0822466



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 4 ... 7 mm, lettering field size: 30 x 4 mm

---

Conductor marker carrier - PATG 4/12 - 0827080



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 6 ... 10 mm, lettering field size: 12 x 4 mm

---

Conductor marker carrier - PATG 4/15 - 1013054



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 6 ... 10 mm, lettering field size: 15 x 4 mm

---

## Insert label - MM-EMT (EX4)R C1 WH/BK - 1169312

### Accessories

Conductor marker carrier - PATG 4/18 - 0820549



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 6 ... 10 mm, lettering field size: 18 x 4 mm

---

Conductor marker carrier - PATG 4/23 - 0808011



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 6 ... 10 mm, lettering field size: 23 x 4 mm

---

Conductor marker carrier - PATG 4/30 - 0822479



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 6 ... 10 mm, lettering field size: 30 x 4 mm

---

Conductor marker carrier - PATG 5/12 - 0803312



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 10 ... 14 mm, lettering field size: 12 x 5 mm

---

Conductor marker carrier - PATG 5/15 - 1013067



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 10 ... 14 mm, lettering field size: 15 x 4 mm

---



## Insert label - MM-EMT (EX4)R C1 WH/BK - 1169312

### Accessories

Conductor marker carrier - PATG 5/18 - 0828059



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 10 ... 14 mm, lettering field size: 18 x 4 mm

---

Conductor marker carrier - PATG 5/23 - 0808024



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 10 ... 14 mm, lettering field size: 23 x 4 mm

---

Conductor marker carrier - PATG 5/30 - 0822482



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 10 ... 14 mm, lettering field size: 30 x 4 mm

---

Conductor marker carrier - PATG 6/15 - 1013070



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 14 ... 22 mm, lettering field size: 15 x 4 mm

---

Conductor marker carrier - PATG 6/18 - 0828062



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 14 ... 22 mm, lettering field size: 18 x 4 mm

## Insert label - MM-EMT (EX4)R C1 WH/BK - 1169312

### Accessories

#### Conductor marker carrier - PATG 6/23 - 0808037



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 14 ... 22 mm, lettering field size: 23 x 4 mm

---

#### Conductor marker carrier - PATG 7/15 - 1013083



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 22 ... 30 mm, lettering field size: 15 x 4 mm

---

#### Conductor marker carrier - PATG 7/23 - 0808040



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 22 ... 30 mm, lettering field size: 23 x 4 mm

---

#### Conductor marker carrier - PATG 8/15 - 1013096



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 30 ... 35 mm, lettering field size: 15 x 4 mm

---

#### Conductor marker carrier - PATG 8/23 - 0808053



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 30 ... 35 mm, lettering field size: 23 x 4 mm

## Insert label - MM-EMT (EX4)R C1 WH/BK - 1169312

### Accessories

Conductor marker carrier - PATG 9/15 - 1013106

Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 35 ... 45 mm, lettering field size: 15 x 4 mm



---

### Marker carriers

Marker carriers - PAB-SK 15 - 1013287

Marker carriers, transparent, unlabeled, mounting type: adhesive, lettering field size: 15 x 4 mm



Marker carriers - PAB-SK 30 - 1013290



Marker carriers, transparent, unlabeled, mounting type: adhesive, lettering field size: 30 x 4 mm