



EAN: 4013288237491

Part number: 05150153001

Article number: 9753

Size: 405x360x60 mm

Weight: 2496 g

Country of origin: CZ

Customs tariff number: 82054000

- Durable foam insert, each tool has its own place; two-coloured, missing tools will quickly be noticed
- One Kraftform Kompakt VDE 817 bitholding screwdriver and 10 blades; individually tested as per IEC 60900
- 1/4" Zyklop ratchet and accessories (sockets, extension, bit adapter, bits)
- Joker 6002 double spanner with practical holding function by a metal plate in the open end
- Joker 6004 S self-setting spanner for bolts and screws of 10-13mm (metric) and 7/16"-1/2" (imperial)
- L-keys (sizes 3 and 4) with hose sleeve, with holding function for hexagonal socket screws, the Hex-Plus profile prevents premature rounding of hexagonal socket screws
- 1 KNIPEX Cobra® High-Tech Water Pump Pliers 87 01 250
- Width x height x depth: without tools 344 x 30 x 392 mm, with tools 344 x 41 x 392 mm

Durable foam insert; two-coloured for quick identification of missing parts; suitable for the Tool Rebel roller cabinets, equipped with one Kraftform Kompakt VDE 817 VDE handle and 10 blades for the following screw profiles: Phillips, Pozidriv, TORX®, hexagonal socket and slotted, one Zyklop Speed ratchet (1/4"), 8 sockets (1/4"), 1 extension (1/4", 50 mm long), one adapter (1/4" square head to 1/4" hexagon) for 1/4" bits, one universal holder for screwdriving machines for 1/4" bits, 16 bits (25 mm long) for the following screw profiles: Phillips, Pozidriv, TORX®, hexagonal socket and slotted; 2 L-keys with holding function for hexagonal socket screws (sizes 3.0 and 4.0), one Joker 6002 double open-end wrench (sizes 17 and 19), one 6004 Joker S self-setting wrench for hexagon screw heads and bolts with wrench sizes 10.0; 11.0; 12.0; 13.0 (metric) or 7/16"; 1/2" (imperial), one KNIPEX Cobra® 87 01 250 high-tech water pump pliers.



Web link

<https://www.wera.de/en/05150153001>

Wera - 9753

05150153001 - 4013288237491


Wera Werkzeuge GmbH

Korzter Straße 21-25


D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de




Safe storage and quick overview



The tools sit securely in the foam thanks to precise contour cutouts, but are easy to remove. The carefully designed arrangement of the tools ensures space-saving storage and quick access to each tool.

Two-coloured foam insert



After removing the tool the light grey second foam becomes visible and therefore missing tools are quickly identified.

Kraftform Kompakt VDE



Testing the tool for dielectric strength at 10,000 volt gives the user the peace of mind that their tool has been tested for its most important property, insulation. Wera VDE tools are subjected to this test piece by piece which guarantees safe working at up to 1,000 volt.

Zyklop "6 in 1"



1. Fine-tooth ratchet 2. Flex-head ratchet 3. Angle ratchet 4. Quick-release ratchet 5. Power ratchet 6. Screwdriver

Double open-ended wrench



The Joker double open-ended wrench is ideally suited for locking down nuts and bolts.

Joker 6004: automatically and continuously self-setting



With its automatically and continuously gripping parallel jaws the Joker spanner 6004 covers all dimensions in the respective field of application. The tool automatically finds the required size when placed on the bolt or screw, no setting required.

Joker 6004: Ratchet mechanism for quick working



The ratchet feature in the jaw ensures fast and consistent screwdriving without removing the tool.

L-keys with holding function for hexagon socket screws



The clamping of the screw is achieved by a flexible locking ball. The holding function is especially helpful in confined, hard-to-reach spaces, where there is no room for a second hand to secure the screw on the tool.

Set contents:

817 VDE Kraftform blade-holding handle, 9 x 98 mm



05003990001

1x 9 x 98 mm



Kraftform Kompakt VDE 60 i Take it easy, 0.4 x 2.5 x 157 mm



05006500001

1x 0.4 x 2.5 x 157 mm



Kraftform Kompakt VDE 60 iS Take it easy, 0.6 x 3.5 x 157 mm



05006506001

1x 0.6 x 3.5 x 157 mm



Kraftform Kompakt VDE 62 iS Take it easy, PH 1 x 157 mm



05006512001

1x PH 1 x 157 mm



05006513001

1x PH 2 x 157 mm

Kraftform Kompakt VDE 65 iS Take it easy, PZ 1 x 157 mm



05006526001

1x PZ 1 x 157 mm



05006527001

1x PZ 2 x 157 mm

Kraftform Kompakt VDE 67 i TORX® Take it easy, TX 10 x 157 mm



05006534001

1x TX 10 x 157 mm



Kraftform Kompakt VDE 67 iS TORX® Take it easy, TX 15 x 157 mm



05006540001

1x TX 15 x 157 mm



05006541001

1x TX 20 x 157 mm

05006542001

1x TX 25 x 157 mm

8000 A Zyklop Speed Ratchet with 1/4" drive, 1/4" x 152 mm



05003500001

1x 1/4" x 152 mm



8790 HMA Zyklop 1/4" socket, 5.5 x 23 mm



05003504001

1x 5.5 x 23 mm

05003505001

1x 6 x 23 mm

05003506001

1x 7 x 23 mm

05003507001

1x 8 x 23 mm

05003509001

1x 10 x 23 mm

05003510001

1x 11 x 23 mm

05003511001

1x 12 x 23 mm

05003512001

1x 13 x 23 mm



8794 SA Zyklop extension with free-turning sleeve, short, 1/4", 1/4" x 75 mm



05003525001

1x 1/4" x 75 mm



Web link

<https://www.wera.de/en/05150153001>

Wera - 9753

05150153001 - 4013288237491

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de

8784 A1 Zyklop bit adaptor, 1/4", 1/4" x 37 mm



05003529001

1x 1/4" x 37 mm



893/4/1 K Universal Bit Holder, 1/4" x 50 mm

05134480001

1x 1/4" x 50 mm



851/1 Z bits, PH 1 x 25 mm

05072070001

1x PH 1 x 25 mm

05072072001

1x PH 2 x 25 mm



855/1 Z bits, PZ 1 x 25 mm



05072080001

1x PZ 1 x 25 mm

05072082001

1x PZ 2 x 25 mm



867/1 TORX® bits, TX 10 x 25 mm



05066485001

1x TX 10 x 25 mm

05066486001

1x TX 15 x 25 mm

05066487001

1x TX 20 x 25 mm

05066488001

1x TX 25 x 25 mm



840/1 Z bits, 3 x 25 mm

05056315001

1x 3 x 25 mm

05056320001

1x 4 x 25 mm

05056325001

1x 5 x 25 mm

05056330001

1x 6 x 25 mm



800/1 Z bits, 0.6 x 4.5 x 25 mm

05072055001

1x 0.6 x 4.5 x 25 mm

05072057001

1x 0.8 x 5.5 x 25 mm

05072059001

1x 1 x 5.5 x 25 mm

05072061001

1x 1.2 x 6.5 x 25 mm



6002 Joker Double Open end wrenches, 17 x 19 x 235 mm

05003765001

1x 17 x 19 x 235 mm



6004 Joker S Self-setting spanner, 10; 11; 12; 13 x 7/16; 1/2" x 154 mm

05020100001

1x 10; 11; 12; 13 x 7/16; 1/2" x 154 mm



950 SPKL HF L-key Multicolour, metric, with holding function, 3 x 123 mm



05022200001

1x 3 x 123 mm

05022201001

1x 4 x 137 mm



Web link

<https://www.wera.de/en/05150153001>

Wera - 9753

05150153001 - 4013288237491

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de

KNIPEX Cobra® High-Tech Water Pump Pliers 87 01 125

1x KNIPEX Cobra® High-Tech Water Pump Pliers 87 01 125




9853 Foam insert Kraftform Kompakt maintenance set 1, without tools, 344 x 30 x 392 mm

05137353001¹⁾

1x 344 x 30 x 392 mm

1) Attention: The foam insert does not fit in the previous model 05501051001 of the roller cabinet.



Web link

<https://www.wera.de/en/05150153001>

Wera - 9753

05150153001 - 4013288237491

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de