

Datasheet

KM6-II subrack system guide, 220mm module

RS Stock number 500-588



KM6-II GUIDES

KM6-EC COMPATIBLE

ONE PART GUIDES

Type 1 PCB

For Eurocards of 1,6mm thickness, either 100mm, 160mm or 220mm long. Compatible with grounding clip. see page 4.35

Type 2 PCB

For Eurocards of 2,4mm thickness, either 160mm or 220mm long.

Type 3 PIU

Plug-in unit (piu) type for cards 111|76 or 245,1mm height, 1,6mm thickness, 160 or 220mm long.

Type 4 PCB

For Eurocards of 1,6mm thickness, 220mm long, this guide will fit over intermediate extrusions, permitting mixing of pcb depths. Compatible with grounding clip. see page 4.35

THREE PART GUIDES

Type 5

Plastic centre section, with aluminium stiffener, for 340mm or 400mm lengths, 1,6mm thickness. Order separately: End feet for pcb or piu.

Type 6

Three part guide end feet for Eurocards of 1,6mm thickness.

Type 7

Aluminium centre section for 340mm or 400mm lengths, 1,6mm thickness. Order separately: End feet for pcb or piu.

Type 8

Three part guide end feet for piu of 1,6mm thickness.

MATERIALS:

Types 1, 3, 4, 6 and 8

Luranyl® 2452/1 or equivalent. Colour green.

Types 2 and 5

Luranyl® 2452/1 or equivalent. Colour black

Type 7

Aluminium extrusion BS 14746063T6

Finish: anodised

Luranyl® 2452/1 is a UL94 VI rated material with a continuous rating of 105°C

ONE PART GUIDES

Ordering information

Guide type	Board length	Order code
1 PCB 1,6mm thick	100	950-242850B
	160	950-232662J
	220	950-232663G
2 PCB 2,4mm thick	160	173-232666F
	220	173-232667D
3 Plug-in-unit	160	950-232664E
	220	950-232665C
4 Low profile	220	950-232668H

One part guides are supplied in packets of 10 but the 160 and 220mm, 1,6 versions are also available in packs of 1000.

1 PCB 1,6mm thick	160	956-243239E
	220	956-243240J

THREE PART GUIDES

Ordering information

Description	Unit	Order code
5 Plastic centre for 340mm board	Pk 10	950-203004E
5 Plastic centre for 400mm board	Pk 10	950-202637D
6 PCB guide feet	10 prs	950-202635H
7 Aluminium centre for 340mm board	Pk 10	950-203005C
7 Aluminium centre for 400mm board	Pk 10	950-202638B
8 Plug-in guide feet	10 prs	950-202636F

KM6-II SUBRACK ACCESSORIES

