



Halogen Classic A-shape

Halogen Classic 70W E27 240V A55 1CT

Philips Halogen Classic light bulbs offer the classical shapes you are used to. This new 'classic' gives high-quality light, is dimmable and starts immediately.

Product data

• General Characteristics

Cap-Base	ES [ES]
Bulb	A55 [A 55mm]
Bulb Finish	Clear
Burning Position	any [Any/Universal]
Nominal Lifetime	2000 hr
Rated Lifetime	2000 hr
Rated Lifetime (years)	2 an

• Light Technical Characteristics

Colour Rendering Index	100 Ra8
Colour Temperature	2800 K
Colour Temperature Technical	2800 K
Lamp Luminous Flux	1200 Lm
Rated Luminous Flux	1200 Lm
Lamp Luminous Efficacy	17.1 Lm/W
LLMF - end nominal lifetime	80 (min) %

• Electrical Characteristics

Rated Wattage	70.0 W
Lamp Wattage	70 W
Technical Lamp	70 W
Power	
Power Factor	1 -
Voltage	240 V
Lamp Current	0.29 A
Dimmable	yes
Wattage Equivalent	92 W
Starting Time	0.0 s

Warm-up Time to 60% Light Outp	instant full light
--------------------------------	--------------------

• Environmental Characteristics

Energy Efficiency Label (EEL)	D
Energy consumption kWh/1000h	70 kWh

• Measuring Conditions

Switching cycle	8000X
-----------------	-------

• Luminaire Design Requirements

Cap-Base Temperature	130 (max) C
----------------------	-------------

• Product Dimensions

Overall Length C	97 (max) mm
Diameter D	56 (max) mm

• Product Data

Order code	251814 02
Full product code	872790025181402
Full product name	Halogen Classic 70W E27 240V A55 1CT
Order product name	Halogen Classic 70W E27 240V A55 1CT/15
Pieces per pack	1
Packing configuration	15
Packs per outerbox	15
Bar code on pack - EAN1	8727900251814

PHILIPS


Halogen Classic A-shape

Bar code on
outerbox - EAN3
Logistic code(s) -
12NC

8718696462355
925699245506

Net weight per piece 25.800 gr

Dimensional drawing



E27

Halogen Classic 70W E27 240V A55 1CT

Product	C (Max)	D (Max)
HalClass 70W E27 240V A55 CL	97	56



© 2015 Koninklijke Philips N.V. (Royal Philips)
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting

2015, September 24
data subject to change