

DCS7485T2-QW

Scie à table XR FLEXVOLT 54V 2Ah Li-Ion Brushless 210 mm

5035048645789



Product Description:

No-load speed (rpm): 5800 Ø Blade/bore (mm): 210 / 30 Blade inclination (°): -3 / 48 Cutting cap. at 90° / 45° (mm): 65 / 45 Max. longitudinal capacity (mm): 610

Product features and benefits:

- EXTENDED RUNTIME: 92 m of 19 mm OSB panels cut on a single charge with a 6 Ah FLEXVOLT battery 3 YEAR WARRANTY: tools covered by an extended warranty, subject to registration FLEXVOLT XR 54V CORDLESS SYSTEM: corded power,
-
- XR FLEXVOLT BRUSHLESS MOTOR 54V: more power and
-
- LARGE CUTTING CAPACITY: 610 mm on the right side of the blade and 318 mm on the left side COMPACT DESIGN: Its weight of 22 kg and optimal size make this the most portable saw in its class RACKS &
- PINIONS: fence lock at the front and back and highly legible graduations for an easy-to-use and easy-to-use saw.
-

Extremely precise

- STEEL ROLL BAR: Protects the saw from drops and impacts on the jobsite CAST IRON TABLE: Designed to ensure precision and accuracy OVERLOAD PROTECTION: Ensures high performance in hard, dry, or frozen woods EASY BEVEL LOCK: Quick bevel lock with highly legible graduations for quick and precise adjustments
-

Specifications techniques :

- [Imperial] Battery Capacity: 6.0 Ah
- Voltage: 54 V Weight (including battery): 23 Kg
- - Depth Rate: Maximum
 - Blade bore: 30 mm
 - Blade diameter: 210 mm
 - - Maximum capacity
 - Edging [right]: 610 mm Table size: 485 x 485 mm Maximum edging capacity

Product Warranty:

This product has a 1-year warranty extended to 3 years after registration

Included Items:

- Batteries (x2)
- Charger (x1)
- 24-tooth carbide blade (x1)
- Miter Guide (x1)
- Keys for mounting the blade (x2)
- Parallel fence (x1)
- Dust Collector Adapter (x1)
- Pusher (x1)

[left]: 318
mm

- Thickness
of ^{saw}
blade: 1.8 mm

DCS7485T2-QW

Scie à table XR FLEXVOLT 54V 2Ah Li-Ion Brushless 210 mm

5035048645789



Product as part of the DCS7485T2-QW composition

Ref	▲ ▼ Title	▲ ▼
DCB118-EU	XR 8A Charger	
DCB546-EC	XR FLEXVOLT 6.0AH BATTERY	
DCS7485T2-EC	54V XR TABLE SAW BARE UNIT TO KIT	
N037466	BAG	
N816302	LABEL BARCODE DCS7485T2-QW TY3	