

Features

- SATA Data
- SATA v3.0
- 6Gbp/s
- Black
- 45cm

RS PRO 0.45m Locking SATA v3 Data Cable - Straight to Straight

RS Stock No. 0839406



RS Professionally Approved Products bring to you, professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

SATA revision 3 doubles the speed of the current 3GB/s version reaching transfer speeds of 6GB/s. The speed ratings of the different versions of Serial ATA are; SATA Revision 1 - 1.5Gb/s SATA Revision 2 - 3Gb/s SATA Revision 3 - 6Gb/s

General Specifications


Connector A	SATA Data
Connector A Style	Straight
Connector B	SATA Data
Connector B Style	Straight
Length	45cm
Outer Sheath Material	PVC
Sheath Colour	Black
SATA Version	V3.0
Data Rate	6 Gbp/s

Approvals

Standards Met	CE UKCA ROHS REACH
---------------	--------------------

Similar Products

Stock No.	Brand	Product Name
0839407	RS PRO	0.45m Locking SATA v2 Data Cable - Straight to Straight
NLRB-302LOCK	RS PRO	0.45m Locking SATA v2 Data Cable - Straight to Straight
NLRB-303LOCK	RS PRO	0.45m Locking SATA v2 Data Cable - Right Angled
NLRB-304LOCK	RS PRO	0.45m Locking SATA v2 Data Cable - Straight to Right Angled
0839406	RS PRO	0.45m Locking SATA v3 Data Cable - Straight to Straight
0839409	RS PRO	0.9m Locking SATA v2 Data Cable - Straight to Straight
NLRB-307LOCK	RS PRO	0.9m Locking SATA v2 Data Cable - Straight to Straight
NLRB-308LOCK	RS PRO	0.9m Locking SATA v2 Data Cable - Right Angled
NLRB-309LOCK	RS PRO	0.9m Locking SATA v2 Data Cable - Straight to Right Angled
0839408	RS PRO	0.9m Locking SATA v3 Data Cable - Straight to Straight



NOTE:

CABLE: 26AWG,UL2725,AL-FOIL,(26AWG*2C+AL)*2C+4D(28AWG),OD=5.0mm,BLACK COLOR,PVC JACKET.

CONNECTORS: SERIAL ATA 7P*2PCS(BLACK INSULATOR,With Latch)

MOLD: MOLDING TYPE.

CONTACTS:

SERIAL ATA 7P	1+4+7	2	3	5	6
SERIAL ATA 7P	1+4+7	2	3	5	6

OPEN/SHORT TEST: 100% TEST.

INSULATION: MIN. 2M.