



SKETCH PRO flipchart

tripod

- Robust flipchart easel for frequent use
- Powder coated steel paper clamp and adjustable paper hooks
- Fits all standard paper pad formats
- Magnetic and dry-wipeable lacquered steel whiteboard surface (H 105 x W 68 cm)
- Attach a flipchart paper pad or use as a whiteboard
- Magnetic fold-out side arms provide additional presentation space
- Height-adjustable: can easily be set at the ideal writing level
- Tripod design with a maximum height of 187 cm and a floor space of W 84 x D 77 cm
- Secured third leg for extra stability
- Easy and tool-free mounting
- Included: free starter kit consisting of: 1x SKETCH ECO paper pad grid, 2x edding 31 EcoLine flipchart marker (specially designed for writing and marking on flipchart paper) as well as a full-width marker tray, two extendable side arms and mounting instructions

- The SKETCH PRO range is built for intensive use, featuring robust materials that ensure long-lasting performance
- This product is made of material from well managed, FSC®-certified forests and other controlled sources (FSC C158462)
- Optimised retail packaging: Attractive and functional packaging enhances product visibility, guiding customers effortlessly to the right solution
- Many SKETCH PRO flipchart parts are detachable, so you can easily replace or fix them if they get damaged
- Board surface guarantee: 5-year guarantee on the perfect writability and wipeability of the board surface when used in combination with Legamaster accessories
- Product guarantee: 5 years

Recommended accessories

- SKETCH ECO paper pad plain 5x 20 sheets (Art.No. 7-157610)
- SKETCH ECO paper pad grid 5x 20 sheets (Art.No. 7-157615)
- SKETCH ECO paper pad plain 2x 50 sheets (Art.No. 7-157620)
- SKETCH ECO paper pad grid 2x 50 sheets (Art.No. 7-157625)

Art.No. **7-152910**

GTIN **8713797111058**





Specifications

Height panel	1070 mm
Width panel	680 mm
Depth panel	16 mm
Height adjustable	Yes
Design of height adjustment	Manual and stepless height adjustment
Height adjustable range	800 mm
Total height (min/max)	1070 / 1870 mm
Pad holder	Yes
Pad holder material	Steel
Paper blocks	Yes
Width side arm	675 mm
Marker tray material	Acrylonitrile butadiene styrene (ABS)
Marker tray length	680 mm
Magnetic	Yes
Surface (material/colour)	Lacquered steel / White
Frame (material/colour)	Acrylonitrile butadiene styrene (ABS) / Black
Carrier material thickness	12 mm
Base	Tripod
Floor space dimensions	845 x 775 mm
Base material	Steel
Number of castors	0
Included accessories	Flipchart paper pad, Marker
Product warranty	5 years
Surface warranty	5 years

Logistics

GTIN	8713797111058
Article number	7-152910
Customs tariff number	940310980000
Quantity	1 piece
Packing dimensions	770 x 120 x 1140 mm
Weight (gross/net)	13.95 kg / 11.10 kg

Product overview

Article name	Article number	GTIN/EAN	Minimum order quantity
Legamaster SKETCH PRO flipchart tripod	7-152910	8713797111058	1