

Bocube Alu

Enclosure with membrane lid, graphite grey, covers anodised, hinged



BA 180806 F-7024

Order no.: 00124124

* = Available on request.

Characteristics

Colour of enclosure group

Graphite grey, similar to RAL 7024

Protection class

IP 66, 68 - 1,2m (2 hours), 69

Enclosure Material

Enclosure: GD Al Si 12, seal PU foamed;

Hinges / covers: Al Mg Si 0.5 powder-coated / natural-coloured anodised

The materials correspond to requirements set R1 or R7 acc. to DIN EN 45545-2 of hazard level HL3.

Scope of delivery

enclosure incl. hinge and fixing material

Important!

To compensate for pressure when temperatures change and cause moisture in the enclosure, we recommend that you use a pressure compensation element.

» Additional information

Technical documentation / Downloads

Technical drawings

3D product data in STEP format: Registration necessary

Product drawing in PDF format: 00124124 BA-180806-F-70243D.pdf (1.2 MB)

Product drawing in DXF format: 00124124 BA-180806-F-7024.dxf (2.8 MB)


20.09.2019

Dimensions

Dimensions

199 x 86 x 60 mm

Product drawing



Product information

Bocube Alu GB.pdf (1.3 MB)

MB)

Drawing for mechanical processing: 00124124 BA-180806-F-7024-G.dxf (2.2 MB)

Milling contours are shown here as a DXF file. (Sub D, USB, HDMI, cable glands, ...)

Assembly Instructions

Bocube-Alu BA Gehaeusemontage Enclosure Assembly 00911501.pdf (183.5 KB)

Works Test Certificates

690 WPZ-Bocube-Alu DE.pdf (178.0 KB)

690 WPZ-Bocube-Alu EN.pdf (172.5 KB)

Matching accessories



Wall brackets

00500104 BA WL 08 - 7024 For BA ..08..



Quick-release fastener

00430109 BA 08 SV-C-0 For BA ..08.. anodized



Pressure compensation membrane DAE

52011000 DAE-D11 Self-adhesive membrane \varnothing 11 mm



Mounting panels, laminated paper, 2 mm

00604100 BA MH 1808 For BA 1808..



DIN rails DIN EN 60715 TH 15, galvanised steel

22151502 TS 15 For BA 1808..



DIN rails DIN EN 60715 G 32, galvanised steel

22321502 TS 32 For BA 1808..



DIN rails DIN EN 60715 TH 35, galvanised steel

22351502 TS 35 For BA 1808..



Screws (SHR) and distance bolts (DIBLZ) for mounting bosses in plastic enclosures

59005049 SHR Z M4x8

KD = 8



Handle set for Bocube Alu, aluminium, powder-coated, silver

00510106* BA GR 08-9006

For BA ..08..