


# PRODUCT DATASHEET

## BLKH CBO RD EYELID 325 WT

BULKHEAD COMBO ROUND EYELID | Attachable half-visor ring for BULKHEAD COMBO luminaires



---

### Areas of application

- Suitable for BULKHEAD COMBO ROUND
- Suitable for indoor and outdoor applications (IP65)





---

### Product features


- Eyelid ring for BULKHEAD COMBO ROUND
- Impact resistance: IK10

## TECHNICAL DATA


## Photometrical data



BLKH CBO RD EYELID V 16W 830




BLKH CBO RD EYELID V 16W 840



BLKH CBO RD EYELID V 16W 857

## Dimensions &amp; Weight

|                |           |
|----------------|-----------|
| Diameter       | 325.00 mm |
| Height         | 77.00 mm  |
| Product weight | 142.00 g  |



BLKH CBO RD EYELID 325 WT

Materials & Colors

|                          |          |
|--------------------------|----------|
| Product color            | White    |
| Housing color            | White    |
| RAL Color (most similar) | RAL 9003 |
| Body material            | ABS      |

Application & Mounting

|                                        |                |
|----------------------------------------|----------------|
| Protection class IK (shock resistance) | IK06           |
| Mounting type                          | Surface        |
| Mounting location                      | Ceiling / Wall |
| Replaceable light source               | No             |

DOWNLOAD DATA

| Documents and certificates                                                         |                                        | Document name      |
|------------------------------------------------------------------------------------|----------------------------------------|--------------------|
|  | User instruction / safety instructions | BLKH CBO RD 325 WT |

| Photometric and lighting design files                                              |                     | Document name                |
|------------------------------------------------------------------------------------|---------------------|------------------------------|
|  | IES file (IES)      | BLKH CBO RD EYELID V 16W 830 |
|  | IES file (IES)      | BLKH CBO RD EYELID V 16W 840 |
|  | IES file (IES)      | BLKH CBO RD EYELID V 16W 857 |
|  | LDT file (Eulumdat) | BLKH CBO RD EYELID V 16W 830 |
|  | LDT file (Eulumdat) | BLKH CBO RD EYELID V 16W 840 |

| Photometric and lighting design files                                            |                                     | Document name                         |
|----------------------------------------------------------------------------------|-------------------------------------|---------------------------------------|
|  | LDT file (Eulumdat)                 | BLKH CBO RD EYELID V 16W 857          |
|  | Light distribution curve type polar | BLKH CBO RD EYELID V 16W 830          |
|  | Light distribution curve type polar | BLKH CBO RD EYELID V 16W 840          |
|  | Light distribution curve type polar | BLKH CBO RD EYELID V 16W 857          |
| Tender texts                                                                     |                                     | Document name                         |
|  | Tender documents                    | BULKHEAD COMBO ROUND EYELID 325 WT-en |

## LOGISTICAL DATA

| Product code  | Packaging unit (Pieces/Unit) | Dimensions (length x width x height) | Gross weight | Volume                 |
|---------------|------------------------------|--------------------------------------|--------------|------------------------|
| 4099854481031 | Folding box<br>1             | 84 mm x 337 mm x 337 mm              | 322.00 g     | 9.54 dm <sup>3</sup>   |
| 4099854481048 | Shipping box<br>10           | 687 mm x 437 mm x 359 mm             | 4618.00 g    | 107.78 dm <sup>3</sup> |

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

## References / Links

– For Guarantee see [www.ledvance.com/guarantee](http://www.ledvance.com/guarantee)

## DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.