

HC-B 24-TFQ-H/O2STM40G - Housing



1412450

<https://www.phoenixcontact.com/gb/products/1412450>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



HEAVYCON B24 sleeve housing, for double locking latch, height: 76 mm, with 2 x M40 thread, straight cable outlet

Commercial data

Item number	1412450
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AF7AAC
Product key	AF7AAC
GTIN	4046356962742
Weight per piece (including packing)	275.74 g
Weight per piece (excluding packing)	275.74 g
Customs tariff number	85389099
Country of origin	DE

HC-B 24-TFQ-H/O2STM40G - Housing



1412450

<https://www.phoenixcontact.com/gb/products/1412450>

Technical data


Notes

General	For contact inserts HC-B24, BB46, BBB64, D64, DD108, M
---------	--

Product properties

Product type	Housing with locking latch
Housing type	Sleeve housing
Application	Standard
Type	B24
No. of cable outlets	2
Type of the screw connection	2x M40
Cable outlet	straight
Pg screw connection	none

Dimensions

Dimensional drawing	
Width	43 mm
Height	76 mm
Length	120 mm

Material specifications

Housing material	Die-cast aluminum
Housing surface material	Powder-coated, gray

Mechanical properties

Mechanical data

Type of the screw connection	2x M40
------------------------------	--------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
Ambient temperature (operation)	-40 °C ... 125 °C

HC-B 24-TFQ-H/O2STM40G - Housing


1412450

<https://www.phoenixcontact.com/gb/products/1412450>



Drawings

Dimensional drawing



Dimensional drawing

HC-B 24-TFQ-H/O2STM40G - Housing



1412450

<https://www.phoenixcontact.com/gb/products/1412450>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1412450>



EAC

Approval ID: RU C-DE.AI30.B.01102

HC-B 24-TFQ-H/O2STM40G - Housing



1412450

<https://www.phoenixcontact.com/gb/products/1412450>

Classifications

ECLASS

ECLASS-13.0	27281101
-------------	----------

ETIM

ETIM 9.0	EC000761
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

HC-B 24-TFQ-H/O2STM40G - Housing



1412450

<https://www.phoenixcontact.com/gb/products/1412450>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk