

FEATURES

- 3/8in socket components
- Chrome Vanadium steel construction
- Sandblasted finish
- Sockets stamp with sizes for quick identification
- Full Allen key set

RS PRO 73 Piece Mechanical Tool Kit with Case

RS Stock No.: 829-6561



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS Pro high quality 72 piece 3/8in socket and hand tool set supplied fitted in a blow moulded carry and storage case to make a comprehensive complete tool kit. The tools are of high-quality and the easy to carry case is versatile and durable with cut-out slots created for each individual component. The kit includes an essential and useful selection of screwdrivers, sockets, spanners and pliers plus extras. Manufactured from high-grade chrome vanadium steel, the tools are strong and built to provide years of service. Each tool has its own locating area in the case which keeps you organised.

General Specifications

Set Type	Mechanical
Set Contents	Bits, Hammer, Hex Keys, Knife, Pliers, Ratchet, Screwdriver, Sockets, Spanners
Number of Pieces	73
Storage Type	Case
Applications	Repair, Maintenance, DIY projects

Kit Contains

Name	QTY
3/8in Quick Release Socket Ratchet	1
3/8in Spark Plug Socket: 16mm	1
3/8in Extension: 75mm	1
3/8in Universal joint	1
3/8in Sockets: 6, 7, 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19mm	14
Hex Key Set: 1.5, 2, 2.5, 3, 4, 5, 6, 8, 10mm	9
300g Hammer	1
160mm Long Nose Plier	1
180mm Combination Pliers	1
250mm Water Pump Pliers	1
200mm Adjustable Wrench	1
Combination Wrench: 8, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19mm	11
Slotted Screwdriver: 5.5 x 100, 6.5 x 150, 6.5 x 38mm	3
Phillips Screwdriver: PH1 x 100, PH2 x 150, PH2 x 38mm	3
Bit Driver	1
Phillips Bit: PH0, PH1, PH2, PH3	4
Pozidriv Bits: PZ0, PZ1, PZ2, PZ3	4
Torx Bits: T10, T15, T20, T25, T30	5
Slotted Bits: 3, 4, 5, 6, 7mm	5
Hex Bits: 3, 4, 5mm	3
Utility Knife	1
Magnetic Pick Up	1
5m Tape Measure	1

Approvals

VDE/1000V Approved	No
--------------------	----

