

1" IMPACT CR-MO SOCKET SET WITH CASE DIN 36-80MM



- Extended Cr-Mo impact socket range in sizes 36, 41, 46, 50, 55, 60, 65, 70, 75 and 80 mm enhancing the set's applicability in heavy industrial tasks
- 6-point metric sockets and impact 3/4" F x 1" M Cr-Mo step up adaptor facilitates secure fitting and adaptability across different tool interfaces
- Inclusion of retaining pins and rings provides added safety and stability during high-torque operations
- TengTools metal carrying case for organised storage and hassle-free mobility
- Compliance with DIN 3129 standards ensures that the set meets the demanding specifications required for industrial-grade power tools

A TengTools 17-piece 1" impact socket set that provides the utmost in versatility and durability for heavy industrial maintenance professionals, offshore engineers, and infrastructure construction teams. Made in strict compliance with DIN 3129 standards, this set is crafted from high-strength Chrome molybdenum (Cr-Mo). Covering 10 socket sizes from 36 to 80mm, and specifically optimized for power tool applications, this expansive set arrives in a robust TengTools metal carrying case.

General information

Country of origin: Taiwan
Barcode: 5020385020504
Tariff code Europe: 8204200000
ECCN US: EAR99
UNSPSC: 27111703

Dimensions

Net weight (g): 20900
Width (mm): 660
Depth (mm): 210
Height (mm): 108

Attributes

Product type: Impact Tool Sets, Socket Sets, Impact Sockets
Number of pieces: 17
Drive: 1"
Socket type: Regular, 6-point
Standard type: DIN
Unit of measurement: Metric

Technical changes and errors may occur. 01-08-2024 19:59



DESIGNED IN SWEDEN

TengTools is a Swedish company present in more than 30 markets worldwide, and offers hand tools in smart storage solutions for demanding professionals within the automotive, maintenance and engineering sectors, as well as motor sport enthusiasts who aspire to use the same tools as top mechanics across the globe.



Sandbergsvägen 3
 441 39 Alingsås, Sweden

LIST OF CONTENTS



9117 1" Impact Cr-Mo socket set with case DIN 36-80 mm

910536 1" Impact Socket DIN Metric 36 mm

910541 1" Impact Socket DIN Metric 41 mm

910546 1" Impact Socket DIN Metric 46 mm

910550 1" Impact Socket DIN Metric 50 mm

910555 1" Impact Socket DIN Metric 55 mm

910560 1" Impact Socket DIN Metric 60 mm

910565 1" Impact Socket DIN Metric 65 mm

910570 1" Impact Socket DIN Metric 70 mm

910575 1" Impact Socket DIN Metric 75 mm

910580 1" Impact Socket DIN Metric 80 mm

940085-C Impact Step Up Adaptor 3/4"F - 1"M DIN

O95034 Retaining Ring 34 x 5.0 mm

O97045 Retaining Ring 45 x 7.0 mm

O97051 Retaining Ring 51 x 7.0 mm

P90435 Retaining Pin 4 x 35 mm

P90545 Retaining Pin 5 x 45 mm

P90551 Retaining Pin 5 x 51 mm