

Spare Fuse Holders, Pullers, Testers and Cabinets

Spare Fuse Holders



Specifications

Description: Spare fuse holders durably constructed using black thermoplastic with common mounting using #6 screws or bolts on 5-inch centers. Dovetailed interlocking between fuse holders simplifies installation and reduces needed hardware. Common footprint allows for any combination of fuse holders to be mounted together. Built-in retaining clips secure fuses.

Flammability Rating: UL 94V0.

Catalog Numbers

| Catalog Numbers | Capacity | For Use With: |
|-----------------|-------------|----------------------|
| TPSFH-CW | 4-position | TPC and/or TPW fuses |
| TPSFH-M | 4-position | TPM fuses |
| TPSFH-LC | 1-position | TPL-C series fuses |
| TPSFH-LB | 1-position | TPL-B series fuses |
| TPSFH-N60 | 1-position | TPN (35-60A) fuses |
| TPSFH-N30 | 4-position | TPN (1-30A) fuses |
| TPSFH-AS | 6-position | TPA & TPS fuses |
| TPSFH-T | 10-position | GMT fuses |

5TPH



Specifications

Description: 5-position spare fuse holder for midsize and Class CC fuses ($\frac{1}{32}$ " diameter) fuses. Constructed of thermoplastic with adhesive tape on back for easy mounting on cabinet doors.

Size: 2.98" W x 1.03" H x 0.63" D

Catalog Number: 5TPH

Data Sheet: 5014

Fuse Pullers



Specifications

Description: Fuse pullers in various sizes to safely and easily extract fuses from blocks and holders.

Catalog Numbers

| Catalog Numbers | Application |
|-----------------|---|
| FP-2 | $\frac{1}{16}$ " to $\frac{1}{8}$ " dia. fuses |
| FP-3 | 1" to 1 $\frac{1}{2}$ " dia. fuses |
| FP-4 | 1 $\frac{1}{2}$ " to 2 $\frac{1}{2}$ " dia. fuses |
| FP-6 | 0-60A T-Tron fuses |
| FP-A3 | Glass Tube & ATC fuses |
| CFP-30 | CUBEFuse 1-30A |
| CFP-60 | CUBEFuse 35-60A |
| CFP-100 | CUBEFuse 70-100A |

Fuse pullers are only to be used when the associated circuit has been de-energized.

FT-2 Fuse Tester



Specifications

Description: Fuse tester for automotive, glass tube and ferrule fuses up to 1 $\frac{1}{2}$ " length. Probe slides to appropriate fuse length. Batteries are included and replaceable.

WARNING: DO NOT test electrical fuses in the fuse panel.

Catalog Number: FT-2

Replacement Battery:
Rayovac 364

SFC Spare Fuse Cabinet



Specifications

Description: Spare fuse cabinet with five cubic feet of storage space. Constructed of heavy gauge steel with durable baked ASA 61 grey enamel finish. Cabinet door is equipped with locking handle for security. Mounting holes are 16 inches on center with key slots.

Size: 24" W x 30" H x 12" D

Material: 0.062 sheet steel

Catalog Numbers:

SFC-FUSE-CAB

SFC-SHELF*

*Extra shelf for fuse cabinet.

Data Sheet: 1119

FT-3 Fuse Tester



Specifications

Description: Fuse tester for automotive, glass tube and ferrule fuses up to 1 $\frac{1}{2}$ " length. Probe slides to appropriate fuse length. Batteries are included and replaceable.

WARNING: DO NOT test electrical fuses in the fuse panel.

Catalog Number: FT-3