

NETGEAR® | AirCard®

AirCard® 790 Mobile Hotspot

Data Sheet

AC790



Highlights

- Secure and ultra-fast 4G LTE and 3G speeds anywhere
- Charge your smartphone with Jump Boost
- Unlocked to networks worldwide†
- Share connection with up to 15 WiFi devices
- Up to 11 hours battery life

Overview

The NETGEAR AirCard 790 Mobile Hotspot gives you a secure and ultra-fast Internet connection anywhere. Unlocked, it's compatible with 4G LTE networks throughout Europe and Asia and with 3G networks worldwide†. You can share a connection with up to 15 WiFi devices and it provides up to 11 hours of battery life. Jump Boost lets you charge your smartphone or tablet.

Ideal Uses



Remote Users

Access to super-fast 4G LTE & 3G connections to the Internet, even if you don't have access to DSL or cable.



Vacationers

Access the web for information and entertainment while on the road and away from home.



Mobile Workers

Make use of downtime while traveling and increase productivity with anywhere, anytime access to high-speed mobile broadband.

Key Features



Jump Boost

Charge your smartphone or tablet with Jump Boost.



Ultra-fast Connectivity with 4G LTE & 3G

Get secure and ultra-fast 4G LTE and 3G speeds anywhere.




Worldwide Access

Unlocked, it's compatible with 4G LTE networks throughout Europe and Asia and with 3G networks worldwide†.



Create a Hotspot

Share a connection with up to 15 WiFi devices. Lithium ion battery provides up to 11 hours of battery life.



SCAN TO LEARN MORE

PACKAGE CONTENTS

- AirCard 790 Mobile Hotspot (AC790)
- Lithium ion battery
- Wall charger
- USB cable with micro USB connector
- Jump Boost cable
- Quick install guide

SPECIFICATIONS

- Dimensions: 110 x 68 x 15.44 mm
- Weight: 136 g
- SIM type: Micro SIM (3FF)
- Active Battery: Up to 11 hours
- Standby Time: Up to 300 hours
- Display: 2.4" Touchscreen

SUPPORTED TECHNOLOGIES

- LTE cat 6 with Carrier Aggregation
- HSPA+/HSPA

SUPPORTED NETWORK BANDS

- 4G LTE: 2100 (B1)/1800 (B3)/2600 (B7)/900 (B8)/800 (B20)/2600 (B38)/2300 MHz (B40)
- 4G LTE CA: B3+B20/B3+B7/B7+B20/B38+B38/B3+B3/B7+B7
- 3G: 850 (B5)/900 (B8)/1900 (B2)/2100 MHz (B1)

WiFi

- 802.11ac/b/g/n
- Dual-Band WiFi 2.4/5 GHz

SYSTEM REQUIREMENTS

- WiFi 802.11b/g/n 2.4/5 GHz enabled device
- Windows 7 and 8 (32/64 bit), Windows RT, Windows Vista (SP2.32/64 bit), XP (SP3 Media Center Editions, 32/64 bit) or Apple Mac compatible OSX 10.6.8 and above

SUPPORT

- Phone support free 90 days from purchase

WARRANTY

- For details visit www.netgear.com/about/warranty/

This product comes with a limited warranty that is valid only if purchased from a NETGEAR authorised reseller.

*Basic technical support provided for 90 days from date of purchase when purchased from a NETGEAR authorised reseller.

† List of supported countries and operators: www.NETGEAR.com/AC790_carriers

ATTENTION: Due to EU law, the country settings must be identical to the country, where the device is operating (important due to non-harmonised frequencies in the EU.)

For indoor use only.

Valid for sale in all EU member states, EFTA states, and Switzerland.

NETGEAR, the NETGEAR Logo, and AirCard are trademarks of NETGEAR, Inc. in the United States and/or other countries. Other brand names mentioned herein are for identification purposes only and may be trademarks of their respective holder(s). Information is subject to change without notice. ©2015 NETGEAR, Inc. All rights reserved.