



Foot protection

GIRO S3S SR

PERFORMANCE

Low-cut shoe with sporty design, combining the highest level of performance with long-lasting comfort.



Specific benefits



Comfort

- Stabilisation of the foot when walking
- Shock-absorbing heel to relieve joint strain
- Padded tongue to reduce pressure points in the lacing area
- Dual-density outsole
- Flexible sole to reduce fatigue during use
- Padded collar for comfort and ankle support

Technologies & labels

 WEAR OFF

 SUPPORT & CUSHION

 TOE CAP SMOOTH EFFECT

Applications

- Building
- Finishing works / Craftsmanship
- Events & scenic
- Heavy industry
- Light industry
- Maintenance

Certifications and norms



EN ISO 20345:2022
S3S CI WPA FO A E ESD SR

Protects against risks



Antistatic



Shock



Cold



Slip



Foot protection

GIRO S3S SR

PERFORMANCE

Low-cut shoe with sporty design, combining the highest level of performance with long-lasting comfort.

Standards - Details

Technical details

Shoe type	Low-cut shoe
Outsole material	PU, 2d
Anti-perforation insert	Metal free
Upper material	Textile, Membrane, TPU
Upper finition material	Knitted
Safety toe-cap	Composite
Lining material	Mesh
Lining material finition	Breathable
Footbed material	PU, Textile
Footbed characteristic	Antistatic, Ergonomic, Removable, Heat barrier, Breathable, Pre-molded
Outsole finition	Injected
Weight (g per shoe)	585
Size range	35 → 49



Safety footwear

GIRO S3S SR

PERFORMANCE

Low-cut shoe with sporty design, combining the highest level of performance with long-lasting comfort.

Logistics information

Reference	Colour	Size	Designation	EAN13	Box code			Weight			
GIROS3S01BKG35 [GIROS3SNG35]	Black-Grey	35	GIRO S3S SR	3295249317805	13295249317802	5	1	6.9 kg	24.4 cm	57.0 cm	32.2 cm
GIROS3S01BKG36 [GIROS3SNG36]	Black-Grey	36	GIRO S3S SR	3295249317959	13295249317956	5	1	7.0 kg	22.5 cm	59.5 cm	34.0 cm
GIROS3S01BKG37 [GIROS3SNG37]	Black-Grey	37	GIRO S3S SR	3295249317966	13295249317963	5	1	7.2 kg	21.6 cm	57.2 cm	33.4 cm
GIROS3S01BKG38 [GIROS3SNG38]	Black-Grey	38	GIRO S3S SR	3295249317973	13295249317970	5	1	7.5 kg	21.6 cm	57.4 cm	32.2 cm
GIROS3S01BKG39 [GIROS3SNG39]	Black-Grey	39	GIRO S3S SR	3295249317980	13295249317987	5	1	7.7 kg	21.8 cm	57.2 cm	32.2 cm
GIROS3S01BKG40 [GIROS3SNG40]	Black-Grey	40	GIRO S3S SR	3295249317997	13295249317994	5	1	8.1 kg	23.8 cm	59.4 cm	33.2 cm
GIROS3S01BKG41 [GIROS3SNG41]	Black-Grey	41	GIRO S3S SR	3295249318000	13295249318007	5	1	8.5 kg	24.2 cm	59.4 cm	34.4 cm
GIROS3S01BKG42 [GIROS3SNG42]	Black-Grey	42	GIRO S3S SR	3295249318017	13295249318014	5	1	8.5 kg	23.6 cm	60.0 cm	34.2 cm
GIROS3S01BKG43 [GIROS3SNG43]	Black-Grey	43	GIRO S3S SR	3295249318024	13295249318021	5	1	8.4 kg	23.4 cm	60.2 cm	34.6 cm
GIROS3S01BKG44 [GIROS3SNG44]	Black-Grey	44	GIRO S3S SR	3295249318031	13295249318038	5	1	9.2 kg	25.4 cm	64.6 cm	36.0 cm
GIROS3S01BKG45 [GIROS3SNG45]	Black-Grey	45	GIRO S3S SR	3295249318048	13295249318045	5	1	9.2 kg	25.4 cm	64.6 cm	36.0 cm
GIROS3S01BKG46 [GIROS3SNG46]	Black-Grey	46	GIRO S3S SR	3295249318055	13295249318052	5	1	9.3 kg	25.0 cm	64.6 cm	36.4 cm
GIROS3S01BKG47 [GIROS3SNG47]	Black-Grey	47	GIRO S3S SR	3295249318062	13295249318069	5	1	10.0 kg	26.4 cm	70.0 cm	38.6 cm
GIROS3S01BKG48 [GIROS3SNG48]	Black-Grey	48	GIRO S3S SR	3295249318079	13295249318076	5	1	10.1 kg	69.8 cm	26.6 cm	38.6 cm
GIROS3S01BKG49 [GIROS3SNG49]	Black-Grey	49	GIRO S3S SR	3295249318086	13295249318083	5	1	10.7 kg	26.4 cm	70.0 cm	38.6 cm



Safety footwear

GIRO S3S SR

PERFORMANCE

Low-cut shoe with sporty design, combining the highest level of performance with long-lasting comfort.



Multiple sales



Minimum sales



Box Width



Box Depth



Box Height