



Description

Professional multi-purpose rust preventative lubricant and dewatering aerosol for use in industry, home and garden. The product is designed to be a multi-functional product offering excellent water displacement characteristics and mild lubricating properties.

- Ideal for inter-process protection of bright metal components which have been subject to water washing
- Ideal for applying to electrical contacts, plugs, points, etc., to expel any moisture affecting the efficiency of the electrical circuitry
- Ideal for lubrication of doors, locks, hinges, belts, windows, latches, zippers, switches, tools, chains, lawn equipment, valves, linkages, pulleys, fans and more
- It is also highly penetrative which aids its usefulness as a water displacing agent and light lubricant
- Based on FUCHS ANTICORIT DWF23 technology

Directions for use

Shake well before use. Hold in an upright position, spraying from a distance of 30cm.

DANGER



Contains: White Spirit, low viscous, Ethoxylated amine Oleic acid derivative. Heterocyclic N-compound. Extremely flammable aerosol. Pressurised container: May burst if heated. Causes skin irritation. Causes serious eye damage. May cause drowsiness or dizziness. Causes damage to organs through prolonged or repeated exposure. Very toxic to aquatic life with long lasting effects. Keep out of reach of children. Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. Do not spray on an open flame or other ignition source. Do not pierce or burn, even after use. Do not breathe dust/fume/gas/mist/vapors/spray. Do not get in eyes, on skin, or on clothing. Avoid release to the environment. Wear protective gloves/protective clothing/eye protection/face protection. IF IN EYES: Rinse cautiously with water for several

minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Immediately call a POISON CENTER/doctor. Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122°F. Dispose of contents/container to an appropriate treatment and disposal facility in accordance with applicable laws and regulations, and product characteristics at time of disposal.

MAXILUBE

Multi-purpose lubricant

Lubricates and penetrates

Solvent deposited

Excellent dewatering characteristics

Creates a damp-proofing film

No CFC propellants - Ozone friendly

High performance aerosol range

500ml e

Made in the UK

650	↻	e
-----	---	---



Part No.
601875557



DE



AT



ES, FR, GB, PT, SK



ES



RU

FUCHS SCHMIERSTOFFE GMBH
Friesenheimer Str. 19 - 68169, Mannheim, Germany
T: +49 (0) 621 3701-0

FUCHS LUBRICANTS (UK) plc
New Century Street • Hanley • Stoke on Trent
T +44 (0) 1782 203700 • www.fuchs.com/uk