





## LIGHT MODULE ELLIPTICAL LIGHT TOWER



**P.N. 190-2817, 190-2818, 190-2819, 190-2820, 190-2821, 190-2822**

Modulo luminoso a led.

*Led luminous module.*  
*Module lumineux à LED*  
*LED-Lichtmodul*  
*Módulo de luz LED*

<b>CUPOLA</b> DOME DOME HAUBE CÚPULA	PC							
<b>GUARNIZIONE</b> GASKET JOINT DICHTUNG JUNTA	O-Ring Silicone							
<b>GRUPPO OTTICO</b> LUMINOUS SOURCE SOURCE LUMINEUSE LICHTQUELLE FUENTE DE LUZ	N°6 LED							
<b>COLORI DISPONIBILI</b> AVAILABLE COLOURS COULEURS DISPONIBLES VERFÜGBARE FARBEN COLORES DISPONIBLES								
<b>TENSIONE DI ALIMENTAZIONE</b> VOLTAGE TENSION SPANNUNG TENSIÓN	24V ac/dc, 240V ac							
<b>SERVIZIO</b> OPERATION FONCTIONNEMENT BETRIEBSART FUNCIONAMIENTO	∞							
<b>CORRENTE NOMINALE</b> CURRENT CONSUMPTION CONSOMMATION DE COURANT STROMAUFNAHME CONSUMO DE CORRIENTE			12 Vdc	12 Vac	24 Vdc	24 Vac	120 Vac	240 Vac
<b>RESA LUMINOSA</b> LIGHT OUTPUT RENDEMENT LUMINEUX LICHT LEISTUNG SALIDA DE LUZ								
<b>MODALITA' LUCE</b> LIGHT EFFECT EFFET LUMINEUX LICHTEFFEKT EFECTO LUMINOSO	Fissa / Lampeggiante <i>Steady/Flashing</i> <i>Fixe/Clignotant</i> <i>Dauerlicht/ Blinklicht</i> <i>Luz fija/ intermitente</i>							
<b>FLASH/MIN</b> FLASHES PER MINUTE ECLATS PAR MINUTE FLASH / MIN FLASHES POR MINUTO	1F X 75, 2F X 90, 3F X 72, 5F X 70							

**Dati diffusi a solo scopo informativo. Sirena S.p.A. puo' modificare i dati in qualsiasi momento senza preavviso.**  
 These data are disclosed only for information purposes. Sirena S.p.A. reserves the right to modify them at any time without prior notice.  
 Les données ne sont divulguées qu'à titre d'information. Sirena S.p.A. se réserve la faculté de les modifier à tout moment sans préavis



**SCHEDA TECNICA**  
Technical data sheet  
Fiche technique

05/09/19

<b>GRADO IP</b> IP RATING DEGRE IP SCHUTZART GRADO IP	IP66
<b>TEMPERATURA DI FUNZIONAMENTO</b> OPERATING TEMPERATURE TEMPERATURE DE SERVICE BETRIEBSTEMPERATUR TEMPERATURA DE FUNCIONAMIENTO	-30°C+50°C
<b>VIBRAZIONI</b> VIBRATIONS VIBRATIONS VIBRATIONEN VIBRACIONES	INDUSTRIAL CEI 60068-2-6 SINE
<b>CERTIFICAZIONI, OMOLOGAZIONI</b> CERTIFICATIONS, APPROVALS CERTIFICATIONS, HOMOLOGATIONS PRODUKTZERTIFIKATE, ZULASSUNGEN CERTIFICADOS, HOMOLOGACIONES	CE
<b>FISSAGGIO</b> MOUNTING FIXATION FIXIERUNG FIJACIÓN	A incastro Stackable A encastrement Stapelbar Apilable
<b>DISEGNO</b> TECHNICAL DRAWING DESSIN TECHNISCHE ZEICHNUNG DIBUJO TECNICO	<p>The technical drawing consists of two views. The left view is a side profile of a rectangular component with a height of 43 and a width of 35. The right view is a top-down view of a circular component with a diameter of 70 and a central rectangular feature with a height of 50.</p>

**Dati diffusi a solo scopo informativo. Sirena S.p.A. puo' modificare i dati in qualsiasi momento senza preavviso.**  
These data are disclosed only for information purposes. Sirena S.p.A. reserves the right to modify them at any time without prior notice.  
Les données ne sont divulguées qu'à titre d'information. Sirena S.p.A. se réserve la faculté de les modifier à tout moment sans préavis