

3m Passive Micro USB to HDMI MHL Cable

Product ID: MHDPM3M



The MHDPM3M 3m Passive Micro USB to HDMI® MHL™ Cable lets you connect your MHL-enabled smartphone, tablet PC or other mobile device to your MHL-enabled HDTV display, monitor, or projector.

This durable cable offers a simple plug-and-play solution for viewing content (e.g. photos, audio and video) from an MHL-enabled mobile device on a large display, and home entertainment system.

Delivering on both quality and convenience, this MHL to HDMI cable supports 1080p video resolution and 7.1 channel digital audio output while simultaneously charging your mobile device when in MHL mode and while connected to your MHL-enabled display.

The MHDPM3M MHL Cable is backed by StarTech.com's Lifetime Warranty, for guaranteed reliability.

Note: As this is a passive cable, your mobile device as well as your HDTV display, monitor, or projector, etc. must be MHL-enabled. Please refer to your devices owner's manual and/or visit the MHL consortium website for a list of [MHL Enabled Products](#). This product will not work with devices that have an 11 pin MHL connector, such as the Samsung S3 and S4 models.

Certifications, Reports and Compatibility



Applications

- Connect your Mobile High-Definition Link (MHL™) enabled device to an MHL-enabled television, monitor or projector through HDMI
- Display video with supporting audio, or share pictures on a full-sized HDMI-capable and MHL-enabled display
- Charge your Micro USB mobile device while connected to your MHL-enabled display

Features

- 1x Micro USB 'B' male connector
- 1x HDMI male connector
- 1080p video output
- Digital audio supported
- TV remote control on your mobile device with CEC supporting HDTVs
- Aluminum-Mylar Foil with Braided Shielding

Hardware	Warranty	Lifetime
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Cable Shield Type	Aluminum-Mylar Foil with Braid
	Connector Plating	Gold
Performance	Audio Specifications	7.1 Surround sound
	Maximum Digital Resolutions	1080p @ 60Hz
	Video Revision	MHL 2.0
Connector(s)	Connector A	1 - HDMI (19 pin) Male
	Connector B	1 - USB Micro-B (5 pin) Male
Physical Characteristics	Cable Length	9.8 ft [3 m]
	Color	Black
	Connector Style	Straight
	Product Height	0.3 in [8 mm]
	Product Length	9.8 ft [3 m]
	Product Weight	4.4 oz [124 g]
	Product Width	0.5 in [12 mm]
	Wire Gauge	24/30 AWG
Packaging Information	Package Quantity	1
	Shipping (Package) Weight	4.7 oz [132 g]
What's in the Box	Included in Package	1 - Passive 3 m MHL Cable

Product appearance and specifications are subject to change without notice.