



## 3/8" INSULATED SOCKET 1000V 12 LONG ZJL-...

### SAM Outillage

10 rue Camille de RochetaillÃ©e  
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â‚¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:55:56





## DESCRIPTION

### 3/8" INSULATED SOCKET 1000V 12 LONG

USE Manual-use sockets suitable for use with a standard ratchet or a mechanically locking ratchet. FEATURES Outer diameter reduced to a minimum for optimal accessibility on installations. Chrome vanadium steel. Socket equipped with four ogive-type recesses inside the female square to accommodate the ratchet's captive ball, ensuring a secure and reliable hold of the assembly. Presence of a collar to provide optimal electrical protection when used with a ratchet or an extension.

## SPECIFIC DATA

| Sales reference | Weight (g) | H (mm) | d (mm) | D (mm) | A (mm) | Guarantee |
|-----------------|------------|--------|--------|--------|--------|-----------|
| ZJL-8           | 50         | 63     | 18     | 14     | 8      | O         |
| ZJL-12          | 60         | 63     | 19     | 19     | 12     | O         |

## SAM Outillage

10 rue Camille de RochetaillÃ©e  
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:55:56



|        |     |    |    |      |    |   |
|--------|-----|----|----|------|----|---|
| ZJL-11 | 60  | 63 | 19 | 18   | 11 | O |
| ZJL-22 | 200 | 63 | 31 | 31   | 22 | O |
| ZJL-13 | 60  | 63 | 20 | 20   | 13 | O |
| ZJL-19 | 120 | 63 | 28 | 28   | 19 | O |
| ZJL-14 | 60  | 63 | 22 | 22   | 14 | O |
| ZJL-10 | 60  | 63 | 18 | 16   | 10 | O |
| ZJL-21 | 150 | 63 | 30 | 30   | 21 | O |
| ZJL-24 | 225 | 63 | 31 | 31   | 24 | O |
| ZJL-18 | 100 | 63 | 28 | 26   | 18 | O |
| ZJL-15 | 80  | 63 | 23 | 23   | 15 | O |
| ZJL-9  | 60  | 63 | 18 | 15.3 | 9  | O |
| ZJL-16 | 80  | 63 | 24 | 24   | 16 | O |
| ZJL-17 | 100 | 63 | 26 | 26   | 17 | O |

#### Guarantee applied

#### O | SAM TOOL guarantee.

Guarantee without time limit on the tools used under normal conditions.

[>> Find out more](#)

#### SAM Outillage

10 rue Camille de RochetaillÃ©e  
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â‚¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:55:56

