



Part Number : [936013620](#)

Product Description : Heavy-Duty Standard (STD) Double Lever Hood, Die-cast Aluminum, with 4 Pegs, Top Entry, Size 24B «104x27», M40 Thread, High Construction, Grey

Series Number : 93601

Status : Active

Product Category : Heavy-Duty Connectors

Engineering Number : 7824.6448.5




Documents & Resources

Drawings

[936013620_sd.pdf](#)

Product Environment Compliance

Compliance

| | |
|--------------------|--|
| GADSL/IMDS | Not Relevant |
| China RoHS |  per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Reviewed per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2022)9120-DC (17 Jan 2023) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

| | |
|----------------|--|
| Status | Active |
| Category | Heavy Duty Connectors |
| Series | 93601 |
| Description | Heavy-Duty Standard (STD) Double Lever Hood, Die-cast Aluminum, with 4 Pegs, Top Entry, Size 24B «104x27», M40 Thread, High Construction, Grey |
| Component Type | Double Lever Hood |
| IP Rating | IP66 |
| Product Name | Heavy-Duty Connectors |
| Standard | ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984 |
| Type | STD |
| UPC | 887191849591 |

Agency

| | |
|-----|---------|
| CSA | 256883 |
| UL | E249674 |

Electrical

| | |
|-------------------|------|
| Voltage - Maximum | 500V |
|-------------------|------|

Physical

| | |
|----------------|------------------|
| Component Size | 24B «104X27» |
| Entry Location | Top |
| Hood Coating | Polyester Powder |

| | |
|---------------------|-------------------|
| Hood Color | GREY RAL 7037 |
| Lock to Mating Part | Yes |
| Material - Hood | Die-cast Aluminum |
| Material - Peg | Stainless Steel |
| Net Weight | 298.000/g |
| Number of Pegs | 4 |
| Packaging Type | Bag |
| Thread Size | M40 |
| Thread Type | (M) Metric |

Mates With / Use With

Use with Part(s)

| Description | Part Number |
|-------------|--|
| Use With | Size 24B «104x27» S-D, S-DD, S-E, S-EE, S-EP, S-ES, S-HSB, S-ESHV, S-K, S-M, and S-EHV Inserts |