

Honeywell Miller H500 Harness

(North America)

Working at height can be a taxing job. Not only are construction workers generally at risk of serious injury or fatality, but long hours spent in a heavy, restrictive harness can be uncomfortable, painful, and cumbersome, leading workers to be less compliant and putting themselves more at risk.

Honeywell recognized the need for change and revolutionized a new generation of light weight safety harnesses. The Honeywell Miller H500 integrates anatomically and ergonomically designed breathable paddings, offers more freedom of movement, and introduces a variety of other new features, including a new smart anti-tangle solution for a hassle-free donning experience.

The Honeywell Miller H500 Safety Harness synthesizes safety, quality, and comfort. Whereas other harnesses protect workers from serious injury at the expense of their long-term well-being, the Honeywell Miller H500 aims beyond compliance to keep workers safe and supported – making your job easier and keeping you safer.

Materials

Webbing	Stretchable Polyester (Neon Green or Black)
Elastic Keepers:	Elastic
Thread:	Polyester
Grommets:	Stainless Steel
*Hardware:	Zinc Plated Steel or aluminum with clear chromate
Back, Shoulder	Nylon
Pads:	EVA Foam
Pad Mesh Shield:	Polyethylene, Polyester
Label Pack:	Polyethylene, Polyester

**All hardware meets ASTM (50) fifty-hour salt spray.*

Technical

Max. Working Load:	420 lbs. (190.5kg)
Webbing Min. Tensile:	5,000 lbs. (22 kN)
*D-Ring Min. Tensile:	5,000 lbs. (22 kN)

Certification

Harness meets OSHA 1926.502, ANSI Z359.11, and **CSA Z259.10

** Harnesses meet variations of CSA classes A, L, and P. See labels for details

Ordering Information

Model Number	Family	Size	Front D-Ring	Side D-Rings	Chest Strap	Leg Strap	Lumbar Pad & Waist Belt	Weight	
								lbs.	kg
H5CC311021	CC1	S/M	none	yes	Mating Buckle	Tongue	yes	5.20	2.36
H5CC311022	CC1	U	none	yes	Mating Buckle	Tongue	yes	5.45	2.47
H5CC311023	CC1	XXL	none	yes	Mating Buckle	Tongue	yes	5.54	2.51
H5CC311121	CC2	S/M	steel	yes	Mating Buckle	Tongue	yes	5.46	2.48
H5CC311122	CC2	U	steel	yes	Mating Buckle	Tongue	yes	5.71	2.59
H5CC311123	CC2	XXL	steel	yes	Mating Buckle	Tongue	yes	5.80	2.63
H5CC312221	CC3	S/M	aluminum	yes	Mating Buckle	Tongue	yes	5.31	2.41
H5CC312222	CC3	U	aluminum	yes	Mating Buckle	Tongue	yes	5.56	2.52
H5CC312223	CC3	XXL	aluminum	yes	Mating Buckle	Tongue	yes	5.65	2.56
Model Number	Family	Size	Front D-Ring	Side D-Rings	Chest Strap	Leg Strap	Lumbar Pad & Waist Belt	Weight	
								lbs.	kg
H5CC222221	CC4	S/M	aluminum	yes	Quick Connect	Quick Connect	yes	5.51	2.50
H5CC222222	CC4	U	aluminum	yes	Quick Connect	Quick Connect	yes	5.73	2.60
H5CC222223	CC4	XXL	aluminum	yes	Quick Connect	Quick Connect	yes	5.80	2.63
H5CC222021	CC5	S/M	none	yes	Quick Connect	Quick Connect	yes	5.36	2.43
H5CC222022	CC5	U	none	yes	Quick Connect	Quick Connect	yes	5.58	2.53
H5CC222023	CC5	XXL	none	yes	Quick Connect	Quick Connect	yes	5.65	2.56
H5CC221121	CC6	S/M	steel	yes	Quick Connect	Quick Connect	yes	5.81	2.64
H5CC221122	CC6	U	steel	yes	Quick Connect	Quick Connect	yes	6.03	2.74
H5CC221123	CC6	XXL	steel	yes	Quick Connect	Quick Connect	yes	6.10	2.77
H5CC311001	CC7	S/M	none	no	Mating Buckle	Tongue	yes	4.90	2.22
H5CC311002	CC7	U	none	no	Mating Buckle	Tongue	yes	5.13	2.33
H5CC311003	CC7	XXL	none	no	Mating Buckle	Tongue	yes	5.20	2.36
H5CS311021	CS1	S/M	none	yes	Mating Buckle	Tongue	yes	6.05	2.75
H5CS311022	CS1	U	none	yes	Mating Buckle	Tongue	yes	6.28	2.85
H5CS311023	CS1	XXL	none	yes	Mating Buckle	Tongue	yes	6.35	2.88
H5CS311121	CS2	S/M	steel	yes	Mating Buckle	Tongue	yes	6.20	2.81
H5CS311122	CS2	U	steel	yes	Mating Buckle	Tongue	yes	6.43	2.92
H5CS311123	CS2	XXL	steel	yes	Mating Buckle	Tongue	yes	6.50	2.95
H5CS221021	CS3	S/M	none	yes	Quick Connect	Quick Connect	yes	6.21	2.82
H5CS221022	CS3	U	none	yes	Quick Connect	Quick Connect	yes	6.43	2.92
H5CS221023	CS3	XXL	none	yes	Quick Connect	Quick Connect	yes	6.50	2.95
H5IC311001	IC1	S/M	none	no	Mating Buckle	Tongue	no	3.42	1.55
H5IC311002	IC1	U	none	no	Mating Buckle	Tongue	no	3.55	1.61
H5IC311003	IC1	XXL	none	no	Mating Buckle	Tongue	no	3.62	1.64
H5IC221001	IC2	S/M	none	no	Quick Connect	Quick Connect	no	3.68	1.67
H5IC221002	IC2	U	none	no	Quick Connect	Quick Connect	no	3.80	1.72
H5IC221003	IC2	XXL	none	no	Quick Connect	Quick Connect	no	3.87	1.75
H5IC222021	IC3	S/M	none	yes	Quick Connect	Quick Connect	no	4.13	1.87
H5IC222022	IC3	U	none	yes	Quick Connect	Quick Connect	no	4.25	1.93
H5IC222023	IC3	XXL	none	yes	Quick Connect	Quick Connect	no	4.32	1.96
H5IC221021	IC4	S/M	none	yes	Quick Connect	Quick Connect	no	4.28	1.94
H5IC221022	IC4	U	none	yes	Quick Connect	Quick Connect	no	4.40	2.00
H5IC221023	IC4	XXL	none	yes	Quick Connect	Quick Connect	no	4.47	2.03
H5IC311121	IC5	S/M	steel	yes	Mating Buckle	Tongue	no	4.27	1.94
H5IC311122	IC5	U	steel	yes	Mating Buckle	Tongue	no	4.40	2.00
H5IC311123	IC5	XXL	steel	yes	Mating Buckle	Tongue	no	4.47	2.03

Model Number	Family	Size	Front D-Ring	Side D-Rings	Chest Strap	Leg Strap	Lumbar Pad & Waist Belt	Weight	
								lbs.	kg
H5IC221101	IC6	S/M	steel	no	Quick Connect	Quick Connect	no	3.68	1.67
H5IC221102	IC6	U	steel	no	Quick Connect	Quick Connect	no	3.80	1.72
H5IC221103	IC6	XXL	steel	no	Quick Connect	Quick Connect	no	3.87	1.75
H5IS311001	IS1	S/M	none	no	Mating Buckle	Tongue	no	3.12	1.42
H5IS311002	IS1	U	none	no	Mating Buckle	Tongue	no	3.35	1.52
H5IS311003	IS1	XXL	none	no	Mating Buckle	Tongue	no	3.42	1.55
H5ISP311001	IS1SP	S/M	none	no	Mating Buckle	Tongue	no	3.32	1.51
H5ISP311002	IS1SP	U	none	no	Mating Buckle	Tongue	no	3.55	1.61
H5ISP311003	IS1SP	XXL	none	no	Mating Buckle	Tongue	no	3.62	1.64
H5IS311021	IS2	S/M	none	yes	Mating Buckle	Tongue	no	3.72	1.69
H5IS311022	IS2	U	none	yes	Mating Buckle	Tongue	no	3.95	1.79
H5IS311023	IS2	XXL	none	yes	Mating Buckle	Tongue	no	4.02	1.82
H5ISP311021	IS2SP	S/M	none	yes	Mating Buckle	Tongue	no	3.87	1.76
H5ISP311022	IS2SP	U	none	yes	Mating Buckle	Tongue	no	4.10	1.86
H5ISP311023	IS2SP	XXL	none	yes	Mating Buckle	Tongue	no	4.17	1.89
H5IS311101	IS3	S/M	steel	no	Mating Buckle	Tongue	no	3.22	1.46
H5IS311102	IS3	U	steel	no	Mating Buckle	Tongue	no	3.45	1.56
H5IS311103	IS3	XXL	steel	no	Mating Buckle	Tongue	no	3.52	1.60
H5IS311121	IS4	S/M	steel	yes	Mating Buckle	Tongue	no	3.82	1.73
H5IS311122	IS4	U	steel	yes	Mating Buckle	Tongue	no	4.05	1.84
H5IS311123	IS4	XXL	steel	yes	Mating Buckle	Tongue	no	4.12	1.87
H5IS221001	IS5	S/M	none	no	Quick Connect	Quick Connect	no	3.23	1.47
H5IS221002	IS5	U	none	no	Quick Connect	Quick Connect	no	3.45	1.56
H5IS221003	IS5	XXL	none	no	Quick Connect	Quick Connect	no	3.52	1.60
H5ISP221001	IS5SP	S/M	none	no	Quick Connect	Quick Connect	no	3.43	1.56
H5ISP221002	IS5SP	U	none	no	Quick Connect	Quick Connect	no	3.65	1.66
H5ISP221003	IS5SP	XXL	none	no	Quick Connect	Quick Connect	no	3.72	1.69
H5ISP111001	IS6SP	S/M	none	no	Mating Buckle	Mating Buckle	no	2.93	1.33
H5ISP111002	IS6SP	U	none	no	Mating Buckle	Mating Buckle	no	3.15	1.43
H5ISP111003	IS6SP	XXL	none	no	Mating Buckle	Mating Buckle	no	3.22	1.46
H5ISP111021	IS7SP	S/M	none	yes	Mating Buckle	Mating Buckle	no	3.53	1.60
H5ISP111022	IS7SP	U	none	yes	Mating Buckle	Mating Buckle	no	3.75	1.70
H5ISP111023	IS7SP	XXL	none	yes	Mating Buckle	Mating Buckle	no	3.82	1.73
H5ISP321001	IS8SP	S/M	none	no	Quick Connect	Tongue	no	3.42	1.55
H5ISP321002	IS8SP	U	none	no	Quick Connect	Tongue	no	3.65	1.66
H5ISP321003	IS8SP	XXL	none	no	Quick Connect	Tongue	no	3.72	1.69
H5ISP221021	IS9SP	S/M	none	yes	Quick Connect	Quick Connect	no	4.03	1.83
H5ISP221022	IS9SP	U	none	yes	Quick Connect	Quick Connect	no	4.25	1.93
H5ISP221023	IS9SP	XXL	none	yes	Quick Connect	Quick Connect	no	4.32	1.96

Toll Free 800.873.5242 (press 4) • hsp techsupport@honeywell.com • www.safety.honeywell.com

⚠ WARNING! THIS DOCUMENT PROVIDES AN OVERVIEW OF FALL PROTECTION PRODUCTS AVAILABLE FROM HONEYWELL AND CARE HAS BEEN TAKEN TO ASSURE THE ACCURACY OF THE DATA. IT DOES NOT PROVIDE IMPORTANT PRODUCT WARNINGS AND INSTRUCTIONS. HONEYWELL RECOMMENDS ALL USERS OF FALL PROTECTION EQUIPMENT UNDERGO THOROUGH TRAINING, AND THAT ALL WARNINGS AND INSTRUCTIONS PROVIDED WITH THE PRODUCTS BE THOROUGHLY READ AND UNDERSTOOD PRIOR TO EACH USE. FAILURE TO READ AND FOLLOW ALL PRODUCT WARNINGS AND INSTRUCTIONS COULD RESULT IN SERIOUS INJURY OR DEATH.

**THE
FUTURE
IS
WHAT
WE
MAKE IT**

Honeywell