



Electrician's slotted screwdriver

TA-...E

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â‚¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 14:00:16





DESCRIPTION



Electrician's slotted screwdriver

Electrician's slotted screwdriver.

End of the blade burnished for greater resistance.

Non-slip handle.

STANDARDS / DIRECTIVES

NF ISO 2380-1, NF ISO 2380-2, DIN 5264

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France


RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 14:00:16



SPECIFIC DATA



Sales reference	L (mm)	Weight (g)	l (mm)	d (mm)	D (mm)	Pattern	Guarantee
TA-25E50	122.8	20	50	2.5	21.9	2,5	O
TA-55E40	92.1	40	40	5.5	33		O
TA-4E150	222.8	60	150	4	21.9	4	O
TA-35E75	147.8	30	75	3.5	21.9	3,5	O
TA-3E50	122.8	20	50	3	21.9	3	O
TA-4E35	92.1	30	35	4	33		O
TA-65E150	263	90	150	6.5	34	6,5	O
TA-4E100	172.8	50	100	4	21.9	4	O
TA-4E40	92.1	30	40	4	33		O
TA-55E125	227.6	80	125	5	31.55	5,5	O
TA-65E40	92.1	40	40	6.5	33		O
TA-2E75	122.8	25	75	2.5	21.9	2	O

Guarantee applied

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 14:00:16



O | SAM TOOL guarantee.

Guarantee without time limit on the tools used under normal conditions.

[>> Find out more](#)

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â‚¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 14:00:16

