

## Electrical Insulating Gloves Class 00 - RIG0011B

Ergonomically designed natural rubber insulating gloves for all-day safety and comfort

Previously known as: E013B



Electrical



Light Duty

## Form-fitting electrical safety gloves, offering versatile protection\* and durable comfort

- **Heightened durability and flexibility:** ActivArm® Electrical Insulating Gloves Class 00 - RIG0011B are made with natural rubber latex, making them both durable and flexible
- **Advanced ergonomics:** These electrical insulated gloves' hand-at-rest shape and non-splayed fingers limit hand fatigue when used continuously
- **Elevated comfort:** A spacious flared cuff means these low-voltage\* electrical gloves grant wearers breathable comfort
- **Specialized defenses:** They are arc flash certified (APC 1 in combination with 96-002 leather protectors) and resistant to acid, ozone and very low temperatures\*\*
- **Increased practicality:** Donning and doffing are simplified by their smooth finish
- **Certified protection:** These insulated gloves also satisfy applicable CSA, NFPA and OSHA standards  
\*Voltage AC maximum 500 V (DC maximum 750)  
\*\*Category A, Z and C respectively



### Industries

- Automotive
- Electrical
- Construction
- Mining
- Machinery and Equipment
- Automotive Aftermarket
- Metal fabrication
- Oil and gas
- Utilities

### Applications

- Applications with risk of touch voltage
- Electrical Contractors
- Hybrid engine manufacturing and repair
- Maintenance Repairs and Operations in all industrial environments (MRO)
- Mass Transit Repair and Maintenance
- Power maintenance, repair & transmission
- Telecom repair near electrical wires

## Electrical Insulating Gloves Class 00 - RIG0011B

Ergonomically designed natural rubber insulating gloves for all-day safety and comfort

Previously known as: E013B

### Key Features

- **Natural rubber latex formulation:** Abrasion resistance and flexibility
- **Ergonomic design:** For electrical PPE that causes limited hand fatigue
- **Generous flared cuff:** Ample space for clothing and ventilation  
\*Arc flash certified as per IEC 614821-2:2014 and ASTM F2675:2021 standards

### Performance Standards & Regulatory Compliance



In-house testing



2111A

### Specifications

| BRAND   STYLE                                             | DESCRIPTION                                                                                                  | Gauge | SIZE                                | LENGTH       | COATING COLOR | PACKAGE                      |
|-----------------------------------------------------------|--------------------------------------------------------------------------------------------------------------|-------|-------------------------------------|--------------|---------------|------------------------------|
| ActivArm Electrical Insulating Gloves Class 00 - RIG0011B | <b>Coating Material:</b> Natural Rubber Latex<br><b>Cuff Style:</b> Straight<br>Cuff with rolled beaded edge |       | 7, 8, 8.5, 9, 9.5, 10, 10.5, 11, 12 | 280mm/11inch | Black         | 1 pair/pack, 10 pairs/carton |

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 900  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Australia

Ansell Limited  
Level 3, 678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jalan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551