

# WS 4-15 - Warning label



1004241

<https://www.phoenixcontact.com/gb/products/1004241>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Warning label, Plate, orange, labeled: Lightning flash and warning in English, mounting type: plug in, for terminal block width: 15 mm, diameter: 0 mm, Number of individual labels: 1



## Your advantages

- The warning labels are secured in the bridge shafts of the UK ... modular terminal blocks using plastic screws
- Mains terminal blocks are reliably covered and marked using warning labels
- Accidental actuation of the terminal points is therefore prevented

## Commercial data

|                                      |                     |
|--------------------------------------|---------------------|
| Item number                          | 1004241             |
| Packing unit                         | 10 pc               |
| Minimum order quantity               | 10 pc               |
| Sales key                            | BG2511              |
| Product key                          | BG2511              |
| Catalog page                         | Page 593 (C-1-2019) |
| GTIN                                 | 4017918011970       |
| Weight per piece (including packing) | 4.79 g              |
| Weight per piece (excluding packing) | 4.36 g              |
| Customs tariff number                | 39269097            |
| Country of origin                    | DE                  |

# WS 4-15 - Warning label



1004241

<https://www.phoenixcontact.com/gb/products/1004241>

## Technical data

### Product properties

|                     |                       |
|---------------------|-----------------------|
| Product type        | Warning label printed |
| Type                | Rectangle             |
| Number of positions | 4                     |
| Pitch               | 15 mm                 |

### Marking

|                             |                                        |
|-----------------------------|----------------------------------------|
| Number of individual labels | 1                                      |
| Printing                    | Lightning flash and warning in English |

### Dimensions

|          |         |
|----------|---------|
| Width    | 60 mm   |
| Height   | 30 mm   |
| Diameter | 0.00 mm |
| Pitch    | 15 mm   |

### Material specifications

|          |        |
|----------|--------|
| Color    | orange |
| Material | PVC    |

### Environmental and real-life conditions

#### Ambient conditions

|                                                     |                  |
|-----------------------------------------------------|------------------|
| Ambient temperature (operation)                     | -15 °C ... 65 °C |
| Recommended ambient temperature (storage/transport) | 23 °C            |
| Recommended humidity (storage/transport)            | 50 %             |

### Standards and regulations

|                 |                             |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

### Mounting

|               |         |
|---------------|---------|
| Mounting type | plug in |
|---------------|---------|

# WS 4-15 - Warning label

1004241

<https://www.phoenixcontact.com/gb/products/1004241>



## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27281107 |
|-------------|----------|

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001777 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 55121700 |
|-------------|----------|

# WS 4-15 - Warning label

1004241

<https://www.phoenixcontact.com/gb/products/1004241>



## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)