



最大100WのUSB Power Delivery規格出力に対応し、ドッキングステーションやドッキングハブを接続したノートパソコンにも安定して給電できるAC充電器。

## ACA-PD93BK

USB PD対応AC充電器 (PD100W・Type-Cケーブル付き)

JANコード 4969887506073



### 仕様

|              |   |
|--------------|---|
| プラグ形状        | 2P  |
| USBポート数      | 1ポート  |
| 使用温度範囲       | 5~35°C  |
| 定格入力         | AC100~240V 50/60Hz  |
| 定格出力電圧/電流    | DC5V/3A、DC9V/3A、DC12V/3A、DC15V/3A、DC20V/5A (最大100W)<br>【PPS】DC3.3~21V/5A (最大100W) |
| USB PD       | 対応  |
| USB出力端子形状    | USB Type-C  |
| 充電ケーブル       | ケーブル付属  |
| ケーブル出力端子形状   | USB Type-C  |
| 合計最大出力       | 100W  |
| USB PD最大対応出力 | 100W  |
| サイズ          | W29×D66×H66mm   |
| 重量           | 約220g   |
| セット内容        | 本体、USB Type-Cケーブル (USB PD 5A対応/ケーブル長2m)、取扱説明書・保証書                                 |

### 特長

最大100WまでのUSB Power Delivery規格による充電に対応したUSB Type-Cケーブル付きのACアダプタです。

USB Type-Cポートからの充電に対応したノートパソコンからタブレット、スマートフォンまで1台で充電可能です。

高出力の100Wに対応しているため、ドッキングステーションやドッキングハブを接続したノートパソコンにも安定して給電できます。

複数の出力ポートを搭載したACアダプタでは、ドッキングハブに接続して使用した場合にACアダプタの空きポートへ他の充電機器を接続すると、ドッキングハブとパソコン間で映像、通信の一時的な切断が発生しますが、本製品は1ポート出力仕様なので他のポートの影響を受けず切断の心配がありません。

機器への充電に使える5A対応のUSB Type-Cケーブルを付属しているため、別途充電ケーブルを用意する必要はありません。

付属のケーブルは長さ2mで、デスク下のコンセントにもゆったり使えます。

USB PD規格による充電は機器を接続するだけで接続機器の仕様に合わせて出力電圧を自動で切替える為、機器に合わせた最適な出力で充電します。

USB PD-PPS規格に対応し、PPS規格対応機種への充電においては充電中の電圧と電流を細かく調整し最適化することで、発熱を抑えながら効率的に充電することができます。

電気用品安全法（PSE）技術基準適合品です。

## 対応情報

|      |   |
|------|---|
| 対応機種 | USB Type-Cポートを搭載しUSB Power Delivery 100Wの規格内での充電に対応したノートパソコン、タブレット、スマートフォン<br>※すべての機種への充電を保証するものではありません。ご使用の機種によっては充電できない場合があります。 |
|------|---|

This AC charger supports USB Power Delivery output of up to 100W, providing reliable power even when connected to a laptop docking station or docking hub.

ACA-PD93BK

USB PD-Compatible AC Charger (PD100W, Type-C Cable Included)

## Specifications

- Plug Type : 2-Pin
- Number of USB Ports : 1
- Operating Temperature Range : 5-35° C
- Rated Input : AC 100-240V 50/60Hz
- Rated Output Voltage/Current  
DC 5V/3A, DC 9V/3A, DC 12V/3A, DC 15V/3A, DC 20V/5A (Max. 100W)  
[PPS] DC 3.3-21V/5A (Max. 100W)
- USB PD : Compatible
- USB Output Terminal : USB Type-C
- Charging Cable : Cable Included
- Cable Output Terminal : USB Type-C
- Total Maximum Output : 100W
- Maximum USB PD Output : 100W
- Dimensions : W29 x D66 x H66mm
- Weight : Approx. 220g
- Set Contents : Main unit, USB Type-C cable  
(USB PD 5A compatible/2m cable length), instruction manual, warranty card

## Features

- This AC adapter comes with a USB Type-C cable that supports charging up to 100W using the USB Power Delivery standard.
- It can charge devices compatible with USB Type-C ports, from laptops to tablets and smartphones, all with a single cable.
- Its high-output 100W output ensures stable power supply even to laptops connected to a docking station or docking hub.
- When using AC adapters with multiple output ports with a docking hub, connecting another charging device to the available port can cause a temporary disconnection of video and communication between the docking hub and the PC. However, this product features a single output port, so there's no need to worry about disconnections due to the lack of interference from other ports.
- It includes a 5A USB Type-C cable for charging devices, eliminating the need for a separate charging cable.
- The included cable is 2m long, allowing it to be easily used in under-desk outlets.
- When using USB PD charging, the output voltage automatically switches to match the connected device's specifications, ensuring optimal charging.
- Compatible with the USB PD-PPS standard, it finely adjusts and optimizes the voltage and current during charging when charging PPS-compatible devices, allowing for efficient charging while reducing heat generation.
- Complies with the technical standards of the Electrical Appliance and Material Safety Act (PSE).