



COMPOSITION OF 189 1000 VOLT TOOLS IN FOAM MODULE

CP-189MM

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â‚¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:51:18





DESCRIPTION

COMPOSITION OF 189 1000 VOLT TOOLS IN FOAM MODULE

Composition of 189 1000V Insulated Tools for 41 Series trolley.

SPECIFIC DATA

Designation	COMPOSITION OF 189 TOOLS 1000 VOLTS IN FOAM MODULE
Sales reference	CP-189MM
Weight (kg)	23.5
Container	foam module
Number of tools	189

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â‚¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:51:18



Compatibility	
Guarantee	O SAM TOOL guarantee.

Guarantee applied

O | SAM TOOL guarantee.

Guarantee without time limit on the tools used under normal conditions.

>> [Find out more](#)

Toolset



x 1

RATCHET MODULE, SOCKETS AND ACCESSORIES INSULATED 1000V 1/4-3/8-1/2
CP-98ZPM



x 10

1000 v insulated 1/4" short sockets

ZRH-...

Ref : 5 - 6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 - 14 mm



x 1

Ratchet 1/4" insulated 1000V Push / Reverse lever

ZR-150



x 1

ADAPTER 1/4" - 3/8" INSULATED

ZR-232



x 1

1000 v insulated 1/4" extensions

ZR-210



x 5

INSULATED 1/4 6-PITCH SCREWDRIVER SOCKET 1000V

ZRS-...

Ref : 3 - 4 - 5 - 6 - 7 mm



x 14

1000V Insulated 3/8" short sockets

ZJH-...

Ref : 7 - 8 - 9 - 10 - 11 - 12 - 13 - 14 - 16 - 17 - 18 - 19 - 21 - 22 mm



x 15

INSULATED 3/8" SOCKET 1000V 12 PANS

ZJ-...

Ref : 8 - 9 - 10 - 11 - 12 - 13 - 14 - 15 - 16 - 17 - 18 - 19 - 21 - 22 - 24 mm



x 1

1000 v insulated 3/8" ratchet

ZJ-159

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:51:18





x 1

ADAPTER 3/8" - 1/2" INSULATED 1000 VOLT
ZJH-232



x 2

1000 v insulated 3/8" extension
ZJ-210 / ZJ-215
Ref : ZJ-210 - ZJ-215



x 1

LOCKING EXTENSION INSULATED 1000V 3/8
ZJ-21...V



x 6

3/8" NON-MAGNETIC TORX INSULATED SOCKET
ZJT-...
Ref : T15 - T20 - T25 - T27 - T30 - T40



x 6

1000 v insulated 3/8" hexagonal screwdriver-socket
ZJS-...
Ref : 3 - 4 - 5 - 6 - 7 - 8 mm



x 16

INSULATED SOCKET 1000V 1/2 6 PANS
ZSH-...
Ref : 8 - 9 - 10 - 11 - 12 - 13 - 14 - 15 - 16 - 17 - 18 - 19 - 20 - 21 - 22 - 23 - 24 mm



x 10

1/2" INSULATED SOCKET 1000V 12 PANS LONG
ZSL-...
Ref : 13 - 16 - 17 - 19 - 21 - 22 - 24 - 27 - 30 - 32 mm



x 1

1000 v insulated 1/2" ratchet
ZS-159



x 2

1000 v insulated 1/2" extensions
ZS-210 / ZS-215
Ref : ZS-210 - ZS-215



x 1

EXTENSION 1/2" INSULATED 1000 VOLT WITH LOCKING
ZS-21...V
Ref : ZS-215V



x 1

1/2" - 3/8" REDUCER INSULATED 1000 VOLT
ZS-232



x 1

T-HANDLE INSULATED 1000V FOR SOCKET
Z-22...



x 1

ISOLATED SCREWDRIVER MODULE 1000V
CP-30ZPM



x 8

SCREWDRIVER ELECTRICIAN INSULATED 1000V
ZTC-...E
Ref : 2x70 - 3x100 - 3,5x120 - 4x120 - 5,5x100 - 6,5x150 - 8x150 - 10x150



x 1

	x 4	SCREWDRIVER PHILLIPS® INSULATED 1000V ZTC-...P Ref : N°0 - N°1 - N°2 - N°3
	x 4	SCREWDRIVER POZIDRIV® INSULATED 1000V ZTC-...PZ Ref : N°0 - N°1 - N°2 - N°3
	x 7	SCREWDRIVER TORX® INSULATED 1000V ZTC-...X Ref : T10 - T15 - T20 - T25 - T27 - T30 - T40
	x 2	SCREWDRIVER PHILLIPS® INSULATED 1000V ZTC-...PBR Ref : N°1 - N°2
	x 2	SCREWDRIVER POZIDRIV® INSULATED 1000V ZTC-...PZBR Ref : N°1 - N°2
	x 3	Screwdriver insulated 1000V Hex female Z-180-... Ref : 7 - 8 - 10 mm

ISOLATED PLIERS MODULE 1000V
CP-17ZPM

	x 1	1000 v insulated slip-joint multigrip pliers Z-201-25
	x 1	1000 v insulated cutting tip pliers Z-230-... Ref : Z-230-16
	x 1	1000 v insulated straight half-round nose pliers Z-237-... Ref : Z-237-16
	x 1	1000V insulated angled half-round nose pliers Z-239-... Ref : Z-239-16
	x 1	1000 v insulated stripping pliers Z-240-16
	x 1	1000 v insulated diagonal cutting pliers Z-233-...P Ref : Z-233-16P
	x 1	1000 v insulated flat nose pliers Z-236-... Ref : Z-236-16

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â‚¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:51:18



	x 1	Ratchet cable cutter insulated. Z-324-32
	x 1	FLAT NOSE NOSE PLIERS INSULATED 1000 VOLT Z-236-C
	x 1	CABLE CUTTER INSULATED 1000 VOLT Z-324-C
	x 1	CURVED NOSE NOSE PLIERS INSULATED 1000 VOLT Z-239-C
	x 1	Set of 2 insulated clips Z-430-AJ2
	x 1	ELECTRICIENME INSULATED 1000 VOLT Z-372
	x 1	1000 v insulated electrician's cutter Z-373
	x 1	ELECTRICIAN SCISSORS INSULATED 1000 VOLT Z-375
	x 1	INSULATED ELECTRICIAN KNIFE 1000 VOLT Z-376
	x 1	ELECTRICIAN KNIFE, RETRACTABLE CERAMIC INSULATED 1000V Z-373-C



x 1

1000V INSULATED WRENCH MODULE
CP-44ZPM

	x 1	1000 v insulated adjustable wrenches Z-54-... Ref : Z-54-8
	x 14	1000 v insulated offset ring wrenches Z-105-... Ref : 6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 - 14 - 16 - 17 - 18 - 19 - 21 mm
	x 6	OPEN-ENDED WRENCH WITH RATCHET 1 INSULATED Z-11-... Ref : 8 - 10 - 13 - 16 - 17 - 19 mm

	x 14	1000 v insulated open end wrenches Z-10-... Ref : 8 - 10 - 11 - 12 - 13 - 14 - 15 - 16 - 17 - 18 - 19 - 21 - 22 - 24 mm
	x 4	1000 v insulated 90° elbow hexagonal wrenches Z-65-... Ref : 3 - 4 - 5 - 6 mm
	x 4	1000 v insulated open socket wrenches Z-80-... Ref : 8 - 10 - 13 - 17 mm
	x 1	1000 v insulated cross wrench Z-87-6-12 Ref : 6x8x10x12 mm