



 PRODUCT-DETAILS

2621 W-53-206

Switch Push button, Single push button 1P+N
1NO 1NC 1CO grey / blue-green - ocean



General Information

Extended Product Type	2621 W-53-206
Product ID	2CKA001484A0054
EAN	4011395023921
Catalog Description	Switch Push button, Single push button 1P+N 1NO 1NC 1CO grey / blue-green - ocean
Long Description	With neutral (transparent) lens. With N terminal. Can be wired as - NO: normally open contact - NC: normally closed contact - CO: change over (two way) contact

Installation

Instructions and Manuals	No document needed
Wiring Diagram	2CKA000097E0034
Mounting Type	Surface Mounted
Type of Fastening	Mounting with Screw
Mounting Orientation	Vertical

Modular Components
Included

Complete Device

Environmental

Degree of Protection IP44

Technical

Data Sheet, Technical Information No document needed

Number of Poles 1P+N

Number of Rocker Switches 1

Actuator Type Push button

Illumination Optional

Electrical

Rated Voltage (U_r) 250 V

Rated Current (I_n) 10 A

Number of Contacts CO 1

Number of Contacts NC 1

Number of Contacts NO 1

Design

Design Range ocean

Surface Finishing Untreated
Matt

Material Thermoplastic

Label Space Provided With Optional Label Space

Label Space Size 57.8 x 9.8 mm

RAL Number Similar to RAL 7035

Color grey / blue-green

Dimensions

Product Net Width 74 mm

Product Net Height 83 mm

Product Net Depth /
Length 55 mm

Product Net Weight 124 g

Engineering

Building Information Modeling – BIM 9AKK108466A8423

Material Compliance

RoHS Declaration	2CKA200000E0447
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
REACH Declaration	2CKA309999E9999
REACH Information	True - contains substances > 0.1 mass percentage
REACH Date	20250901
Conflict Minerals Reporting Template (CMRT)	9AKK108468A3363
SCIP	f49e6368-1464-40c6-ac41-c99dfcc79bdb Germany
Simplified SCIP	f49e6368-1464-40c6-ac41-c99dfcc79bdb Germany
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
WEEE B2C / B2B	Business To Consumer

Certificates and Declarations

Declaration of Conformity - CE	2CKA100000E0335
EU Data Act Applicability and Compliance	Not Applicable

External Classifications and Standards

ETIM 9	EC000029 - Push button
ETIM 10	EC000029 - Push button
eClass	V11.0 : 27144044

Accessories

Identifier	Description	Type	Quantity	Unit Of Measure
2CKA001761A1490	Cable bushing blue green - ocean	2138 W-53	1	piece
2CKA001761A1492	Cable Entry blue green - ocean	2086 W-53	1	piece
2CKA001714A0294	Symbol red	2622-12-101	1	piece
2CKA001714A0286	Symbol with Symbol "key" clear transparent	2622 TR-101	1	piece
2CKA001714A0278	Symbol with Symbol "bell" clear transparent	2622 KI-101	1	piece
2CKA001714A0260	Symbol with Symbol "light" clear transparent	2622 LI-101	1	piece
2CKA001714A0252	Symbol clear transparent	2622 N-101	1	piece
2CKA001784A0719	Illumination set for Switch/push button White Incandescent lamp, 40 mA, 24 V AC/DC	8358	1	piece
2CKA001784A0321	Illumination set for Switch/push button Orange Neon lamp, 1 mA, 230 V	8346-1	1	piece
2CKA001784A0529	Illumination set for Switch/push button White Incandescent lamp, 40 mA, 12 V	8335-1	1	piece
2CKA001784A0024	Illumination set for Switch/push button White Incandescent lamp, 40 mA, 3 ... 8 V	8333-1	1	piece
2CKA001784A0016	Illumination set for Switch/push button Orange Neon lamp, 0.6 mA, 230 V	8332-1	1	piece
2CKA001784A0777	Illumination set Label holder LED 1 mA, 230 V clear transparent - ocean	2152 NLI-53	1	piece
2CKA001799A0882	Label Holder transparent - ocean	1763-53	1	piece
2CKA001716A0042	Mounting Plate 1-gang brass	2609 WS	1	piece
2CKA001761A1491	Cable Entry blue green - ocean	2139 W-53	1	piece
2CKA001761A1489	Cable Entry blue green - ocean	2136 W-53	1	piece
2CKA001761A1503	Cable Entry blue green - ocean	2137/10 W-53	1	piece
2CKA001761A1506	Cable Entry blue green - ocean	2137/11 W-53	1	piece

Categories

Low Voltage Products and Systems → Wiring Accessories - Light Switch Ranges → Surface Mounted Range → Mechanical Controls



360