

Pipeline markers - PML-T108 (52X560)R CUS - 1014264

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Pipeline markers, can be ordered: By line, brown/red, labeled according to customer specifications: Flammable liquids, Mounting type: Adhesive, Lettering field: 52 x 560 mm



Why buy this product

☒ Group 8 (combustible liquids)



Key commercial data

Packing unit	1
GTIN	 4 046356 784702
Custom tariff number	39199000

Technical data

Dimensions

Length (b)	52 mm
Width (a)	560 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
---------------------------------	-------------------

General

Color	brown/red
Type	Rectangle
Components	Silicone-free
Material	Polyester
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Printing	Flammable liquids
Number of individual labels per row	1
Marking mounting type	Adhesive

Pipeline markers - PML-T108 (52X560)R CUS - 1014264

Classifications

eCl@ss

eCl@ss 4.0	27141199
eCl@ss 4.1	27141199
eCl@ss 5.0	27371301
eCl@ss 5.1	27371301
eCl@ss 6.0	27371301
eCl@ss 7.0	27371301
eCl@ss 8.0	27141137

ETIM

ETIM 3.0	EC000712
ETIM 4.0	EC002498
ETIM 5.0	EC001777

UNSPSC

UNSPSC 6.01	43172501
UNSPSC 7.0901	43212107
UNSPSC 11	43172501
UNSPSC 12.01	43212107
UNSPSC 13.2	43212107

Accessories

Accessories

Warning label printed

Hazardous substances label - PML-GHS101 (13X13) - 1014269



Hazardous substances label, Sheet, red/white, labeled: Explosive, Mounting type: Adhesive, Lettering field: 13 x 13 mm

Hazardous substances label - PML-GHS101 (25X25) - 1014270



Hazardous substances label, Sheet, red/white, labeled: Explosive, Mounting type: Adhesive, Lettering field: 25 x 25 mm

Pipeline markers - PML-T108 (52X560)R CUS - 1014264

Accessories

Hazardous substances label - PML-GHS102 (13X13) - 1014271



Hazardous substances label, Sheet, red/white, labeled: Flammable, Mounting type: Adhesive, Lettering field: 13 x 13 mm

Hazardous substances label - PML-GHS102 (25X25) - 1014272



Hazardous substances label, Sheet, red/white, labeled: Flammable, Mounting type: Adhesive, Lettering field: 25 x 25 mm

Hazardous substances label - PML-GHS103 (13X13) - 1014273



Hazardous substances label, Sheet, red/white, labeled: Oxidizing, Mounting type: Adhesive, Lettering field: 13 x 13 mm

Hazardous substances label - PML-GHS103 (25X25) - 1014274



Hazardous substances label, Sheet, red/white, labeled: Oxidizing, Mounting type: Adhesive, Lettering field: 25 x 25 mm

Hazardous substances label - PML-GHS104 (13X13) - 1014275



Hazardous substances label, Sheet, red/white, labeled: Pressurized gases, Mounting type: Adhesive, Lettering field: 13 x 13 mm

Pipeline markers - PML-T108 (52X560)R CUS - 1014264

Accessories

Hazardous substances label - PML-GHS104 (25X25) - 1014276



Hazardous substances label, Sheet, red/white, labeled: Pressurized gases, Mounting type: Adhesive, Lettering field: 25 x 25 mm

Hazardous substances label - PML-GHS105 (13X13) - 1014277



Hazardous substances label, Sheet, red/white, labeled: Corrosive, Mounting type: Adhesive, Lettering field: 13 x 13 mm

Hazardous substances label - PML-GHS105 (25X25) - 1014278



Hazardous substances label, Sheet, red/white, labeled: Corrosive, Mounting type: Adhesive, Lettering field: 25 x 25 mm

Hazardous substances label - PML-GHS106 (13X13) - 1014279



Hazardous substances label, Sheet, red/white, labeled: Toxic, Mounting type: Adhesive, Lettering field: 13 x 13 mm

Hazardous substances label - PML-GHS106 (25X25) - 1014280



Hazardous substances label, Sheet, red/white, labeled: Toxic, Mounting type: Adhesive, Lettering field: 25 x 25 mm

Pipeline markers - PML-T108 (52X560)R CUS - 1014264

Accessories

Hazardous substances label - PML-GHS107 (13X13) - 1014281



Hazardous substances label, Sheet, red/white, labeled: Irritant, Mounting type: Adhesive, Lettering field: 13 x 13 mm

Hazardous substances label - PML-GHS107 (25X25) - 1014282



Hazardous substances label, Sheet, red/white, labeled: Irritant, Mounting type: Adhesive, Lettering field: 25 x 25 mm

Hazardous substances label - PML-GHS108 (13X13) - 1014283



Hazardous substances label, Sheet, red/white, labeled: Hazardous to health, Mounting type: Adhesive, Lettering field: 13 x 13 mm

Hazardous substances label - PML-GHS108 (25X25) - 1014284



Hazardous substances label, Sheet, red/white, labeled: Hazardous to health, Mounting type: Adhesive, Lettering field: 25 x 25 mm

Hazardous substances label - PML-GHS109 (13X13) - 1014285



Hazardous substances label, Sheet, red/white, labeled: Hazardous to the environment, Mounting type: Adhesive, Lettering field: 13 x 13 mm

Pipeline markers - PML-T108 (52X560)R CUS - 1014264

Accessories

Hazardous substances label - PML-GHS109 (25X25) - 1014286



Hazardous substances label, Sheet, red/white, labeled: Hazardous to the environment, Mounting type: Adhesive, Lettering field: 25 x 25 mm

Warning label unprinted

Hazardous substances label - US-PML-GHS100 (13X13) - 1014287



Hazardous substances label, Card, red/white, Pre-printed, can be labeled with: THERMOMARK CARD, Mounting type: Adhesive, Lettering field: 13 x 13 mm

Hazardous substances label - US-PML-GHS100 (25X25) - 1014288



Hazardous substances label, Card, red/white, Pre-printed, can be labeled with: THERMOMARK CARD, Mounting type: Adhesive, Lettering field: 25 x 25 mm

Hazardous substances label - PML-GHS100 (13X13)R - 1014289



Hazardous substances label, Roll, red/white, Pre-printed, can be labeled with: THERMOMARK ROLL, THERMOMARK X, Mounting type: Adhesive, Lettering field: 13 x 13 mm

Hazardous substances label - PML-GHS100 (25X25)R - 1014290



Hazardous substances label, Roll, red/white, Pre-printed, can be labeled with: THERMOMARK ROLL, THERMOMARK X, Mounting type: Adhesive, Lettering field: 25 x 25 mm
