


MPI001/RP/GN/12 Datasheet

 [View Product Page](#)

Product Name // **Stainless Steel Vandal Resistant
Illuminated IP66 Push Button Switch MPI001 Series 12V
Green LED Dot Solder Tag Termination**



// **Product Description:**

- Stainless Steel Illuminated Vandal Resistant Push Button Switches
 - 22mm diameter
 - Single Contact, push to make, tactile (momentary action)
 - Choice of Termination, depending on part code:
 - /28 - 2.8mm Tab
 - /TE or /TERM - Screw Terminal
 - /RP - Solder Tag
 - /FL - 300mm Flying Leads; white - switch, red - LED +, black - LED -
 - Choice of Illumination style depending on part code:
 - Part codes prefixed MPI001 - Centre dot
- Part codes prefixed MPI002 - Ring
 - Choice of LED colour depending on part code:
 - Single colour: /RD - Red, /GN - Green, /AM - Amber, /BL - Blue, /WH - White
 - Dual colour (only available in /28 2.8mm Tab and /TE Screw Terminal versions): /D1 - Red/Green, /D4 - Red/Blue, /D5 - Green/Blue
 - (When dual colour LEDs are forward biased the first colour is lit, when reverse biased the second colour is list)
 - Choice of LED operating voltage depending on part code suffix:
 - Resistor installed for operation at a single fixed voltage: /6 - 6V DC, /12 - 12V DC, /24 - 24V DC
 - Also available with no resistor installed (no suffix) - see data for ratings to enable calculation of suitable series resistor value for application
 - Front panel seal to IP66 (microswitch not sealed). /RP Solder Tag versions are also rear panel sealed to IP66

// **General Information:**

Product Display Title:	Stainless Steel Illuminated Vandal Resistant Push Button Switches
Product Family:	Switches
Product Series:	Push Button
Body Material:	SS 304
Current Max:	0.05A
Diameter:	22mm
Function:	Momentary Action
Illumination Colour:	Green
Illumination Shape:	Dot
Illumination Style:	Illuminated
Illumination Voltage:	12V
Ip Rating:	IP66
Max Operating Temperature:	+70°C
Min Operating Temperature:	-30°C
Thread Size:	0.747inch x 26TPI
Voltage Max:	24V

// **Product PDF Links**

 [Vandal Resistant switches product...](#)

// **Product 3D CAD Model Links**

 [MPI001/RP/GN/123D CAD Model](#)



Have a question or project enquiry
you'd like to talk to us about?



[Click Here To Contact Us](#)