

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

LOC
AJ

DIST
16

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	P	REVISED PER ECO-11-005030	11MAR11	RK	HMR
	R	REVISED PER ECO-12-018113	27DEC2012	TD	AC

1. SEE I.S. 408-1914-1

2

REMOVE FOIL TO OUTER JACKET

3

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

4.78
[.188]

11.13
[.438]

5.56
[.219]

15.90
[.626] REF

Ø14.53 MAX
[.572]

A MAX

RECOMMENDED STRIP LENGTH

OBSOLETE	2	RG-188 DOUBLE BRAID	220009-1	30.94 [1.218]	21427-2	9-329049-0	1-331352-2	3-331349-1	3	5-5225395-6		
		BELDEN 88240, HI-TEMP RG-58/U, BERK-TEK BTDC 58	69478-1	34.14 [1.344]	-	9-228783-0	1-331357-3	2-331349-9		4-5225395-2		
		HI-TEMP RG-62A/U, TIMES PL62, BELDEN 88241, BERK-TEK BTDC 59 & 62	69477-1	34.14 [1.344]	-	9-228784-0	2-331352-3	3-331349-0		4-5225395-1		
		BELDEN 8212	69477-1	30.94 [1.218]	-	9-50428-0	1-331352-7	3-331349-0		2-5225395-0		
		AMPHENOL 21-597	69477-2	30.94 [1.218]	-	9-329461-0	1-331352-2	3-331349-1		1-5225395-0		
		RG-179/U, 187/U	220009-1	30.94 [1.218]	21427-2	9-328666-0	1-331352-4	3-331349-1		5225395-8		
		RG-174/U, 188/U	220009-1	30.94 [1.218]	21427-2	9-328666-0	1-331352-2	3-331349-1		5225395-7		
		RG-142/U, 142A/U, 142B/U	69478-1	30.94 [1.218]	-	9-329099-0	1-331357-4	2-331349-9		5225395-6		
		RG-141/U & 141A/U	69478-1	30.94 [1.218]	-	9-50427-1	1-331357-4	2-331349-9		5225395-5		
		RG-55/U, 55A/U, 55B/U, 223/U	69478-1	30.94 [1.218]	-	9-329099-0	1-331357-3	2-331349-9		5225395-3		
	RG-59/U, 59A/U, 59B/U, 62/U, 62A/U, 62B/U	69477-1	30.94 [1.218]	-	9-50428-0	2-331352-3	3-331349-0		5225395-2			
	RG-58/U, 58A/U, 58B/U, 58C/U	69478-1	30.94 [1.218]	-	9-50427-1	1-331357-3	2-331349-9		5225395-1			
	FOR USE WITH CABLE	CRIMP TOOL	A	4	SLEEVE QTY=1	3	FERRULE QTY=1	2	CONTACT QTY=1	1	PLUG ASSEMBLY QTY=1	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

0 PLC ± -

1 PLC ± -

2 PLC ± 0.041 [.016]

3 PLC ± -

4 PLC ± -

ANGLES ± -

MATERIAL -

FINISH -

DWN
A. FERNANDEZ-DOCK5
CHK
J. HAVENER
APVD
J. LIPPERT
PRODUCT SPEC
108-12020
APPLICATION SPEC
-
WEIGHT -

31JAN2005
31JAN2005
31JAN2005

CUSTOMER DRAWING

TE Connectivity

PLUG
DUAL CRIMP,
BNC

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=5225395

RESTRICTED TO
-

SCALE
2:1

SHEET
1 of 1

REV
R

1471-9 (3/11)

5225395