


Product datasheet

Specifications



"PanelSeT S3D seismic plain door with mount.plate - H300xW250xD150 - IP65 - IK10"

Local distributor code:

402657873

NSYS3D6G32515P

⚠ Discontinued on: 9 Feb 2023

⚠ Discontinued

EAN Code: 3606480793943

Main

Range	PanelSeT
product name	S3D 6G
Enclosure application	Seismic
Product or component type	Enclosure
Enclosure nominal height	300 mm
Enclosure nominal width	250 mm
Enclosure nominal depth	150 mm
Door type	Plain
Mounting plate description	Reinforce
Enclosure mounting	Wall mounted
Device composition	1 x body 1 x door 1 x lock 2 x fixing bracket 1 x mounting plate 1 x earthing components door and lock 1 x cable gland plate
Continuity of earth	Earthing connection between body and door

Complementary

Body type	Single piece body Gutter-shaped front rail
Number of doors	Front face: 1 door(s)
Door opening side	Right (120 °)
Lock type	1-point closure
Type of keylock	405E
Type of operating handle	Lock button
Accessibility for operation	Front
Removable parts	Cable gland plate by screws
Material	Steel
Thickness	Body: 2 mm Door: 2 mm Cable gland plate: 1.5 mm
Surface finish	Epoxy-polyester powder
Colour	Grey (RAL 7035)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Net weight	9 kg
------------	------

Environment

Surface treatment	87 % decontaminable painting conforming to NF T 30-501.
Standards	IEC 62208 EDF CRT 91 C 112 00
IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262
Seismic performance	Seismic tests 6G conforming to EDF CRT 91 C 112 00

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	21.000 cm
Package 1 Width	33.000 cm
Package 1 Length	35.000 cm
Package 1 Weight	8.820 kg
Unit Type of Package 2	PAM
Number of Units in Package 2	20
Package 2 Height	93.000 cm
Package 2 Width	100.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	188.400 kg

Logistical informations

Country of origin	FR
-------------------	----

Contractual warranty

Warranty	18 months
----------	-----------



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	83
---	----

Use Better



Materials and Substances

Packaging made with recycled cardboard	No
--	----

Packaging without single use plastic	No
--------------------------------------	----

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
-----------------------------------	--

SCIP Number	E893f0a0-d2cc-4011-9425-3873dde70142
-------------	--------------------------------------

REACH Regulation	REACH Declaration
------------------	-----------------------------------

Use Again



Repack and remanufacture

Take-back	No
-----------	----