

- Halogen retrofit, will fit into every GU10 / GZ10 socket.
- Coloured LED light appears much richer than the light from coloured halogen, fluorescent or HID lamps.
- Ideal for creating ambience atmosphere, in both domestic and semi-professional
- Applications e.g. Hotel rooms, Restaurants, Bars, Furniture lighting etc.
- Life time of 25,000 hours, low maintenance cost.

Code	Description	Volts	Colour Name	Colour	Colour Temp	Watts	Cap	Luminous Flux	Average Rated Life	Box Qty
<b>RefLED</b>										
26746	Hi-Spot RefLED E550 25° Non-Dim	200-250V	Homelight	827	2700K	7.5W	GU10	350 lm	25000 hrs	15
26748	Hi-Spot RefLED E550 40° Non-Dim	200-250V	Homelight	827	2700K	7.5W	GU10	350 lm	25000 hrs	15
26747	Hi-Spot RefLED E550 25° Non-Dim	200-250V	Warm white	830	3000K	7.5W	GU10	350 lm	25000 hrs	15
26749	Hi-Spot RefLED E550 40° Non-Dim	200-250V	Warm White	830	3000K	7.5W	GU10	350 lm	25000 hrs	15
26770	Hi-Spot RefLED E550 25° Non-Dim	200-250V	Cool White	840	4000K	7.5W	GU10	385 lm	25000 hrs	15
26771	Hi-Spot RefLED E550 40° Non-Dim	200-250V	Cool White	840	4000K	7.5W	GU10	385 lm	25000 hrs	15
26725	HI-SPOT RefLED PAR16 GU10 8W 2700K	220-240V	Homelight	827	2700K	8W	GU10	300 lm	35000 hrs	10
26400	HI-SPOT RefLED PAR16 GU10 8W 3000K	220-240V	Warm White	830	3000K	8W	GU10	300 lm	35000 hrs	10

<b>RefLED</b>										
26705	Hi-Spot RefLED PAR 20	100-250V	Warm white	830	3000K	5.5W	E27	300 lm	30000 hrs	6
26707	HI-SPOT RefLED PAR30 11W	100-250V	Warm White	830	3000K	11W	E27	610 lm	30000 hrs	6
26500	HI-SPOT RefLED PAR38 15W outdoor	100-250V	Warm White	830	3000K	15W	E27	750 lm	30000 hrs	6
26315	RefLED SA111 10°	12V AC/DC	Warm White	830	3000K	11W	G53	360 lm	25000 hrs	6
26316	RefLED SA111 25°	12V AC/DC	Warm White	830	3000K	11W	G53	360 lm	25000 hrs	6
26317	RefLED SA111 40°	12V AC/DC	Warm White	830	3000K	11W	G53	360 lm	25000 hrs	6

<b>RefLED</b>										
26772	Dim RefLED E550 2700K 350 lm 25°	200-250V	Homelight	827	2700K	TBCW	GU 10	350 lm	25000 hrs	6
26773	Dim RefLED E550 3000K 350 lm 25°	200-250V	Warm White	830	3000K	TBCW	GU 10	350 lm	25000 hrs	6
26774	Dim RefLED E550 4000K 350 lm 25°	200-250V	Cool White	840	4000K	TBCW	GU 10	385 lm	25000 hrs	6
26775	Dim RefLED E550 2700K 350 lm 40°	200-250V	Homelight	827	2700K	TBCW	GU 10	350 lm	25000 hrs	6
26776	Dim RefLED E550 3000K 350 lm 40°	200-250V	Warm White	830	3000K	TBCW	GU 10	350 lm	25000 hrs	6
26777	Dim RefLED E550 4000K 350 lm 40°	200-250V	Cool White	840	4000K	TBCW	GU 10	385 lm	25000 hrs	6