

Product data sheet

Specifications



Repacked, Apparatus box, Multifix Air, single, 20/32A, 85 x 47 mm, white

IMT35034W



This repacked option saves 5.297 over the standard condition

Main

Range of product	Multifix
Product name	Multifix Air
Product or component type	Apparatus box
Device application	For airtight installation
Device presentation	Without cover

Complementary

Product destination	20 A socket-outlet 32 A socket-outlet
Function available	Anti-rotation system Extra space for cables
Number of gangs	1 gang
fixing mode	By screws
Material	PP/TPE
Mechanical robustness	Airtight Fire resistance
Colour tint	White (RAL 9010)
Cable entry	2 knock-outs conduit of 16...20 mm diameter 2 knock-outs conduit of 20...25 mm diameter
Distance between centers	71 mm
drill diameter/depth	85 mm 47 mm
Distance between supports	78 mm
Height	88 mm
Width	84 mm
Depth	47 mm

Environment

Ambient air temperature for operation	-5...60 °C
IP degree of protection	IP40
fire resistance	850 °C
Standards	EN 60670-1

Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.500 cm
Package 1 Width	9.500 cm
Package 1 Length	9.500 cm
Package 1 Weight	33.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	11.500 cm
Package 2 Width	20.100 cm
Package 2 Length	32.700 cm
Package 2 Weight	448.000 g
Unit Type of Package 3	S04
Number of Units in Package 3	50
Package 3 Height	30 cm
Package 3 Width	40 cm
Package 3 Length	60 cm
Package 3 Weight	3.058 kg

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Lower carbon footprint

5 kg CO2 eq.

Use Better



Materials and Substances

EU RoHS Directive

[Compliant](#)

REACH Regulation

[Free of Substances of Very High Concern above the threshold](#)

Use Longer



Lifetime extension

Repair

No

Use Again



Repack and remanufacture

Take-back

No