


8986 FP-3-1/4-B foot valve with detent - Series: All



8986 FP-3-1/4-B foot valve with detent - Series: All

Pos.	Part no.	Type	Note	Qty.	Unit
A	673551	FP-3-1/4-B / FP-5-1/4-B Assortment of spare parts	Spare parts: 7, 10, 11, 12, 13, 14, 15, 17, 18, 20, 21, 24, 25, 26, 29	1	PC
1	200680	ISO 4762-M5X60-8.8 Socket head screw		2	PC
2		FP -3-1/4 Cover	Not available	1	PC
3	200566	DIN 84-M5X60-4.8 Socket head screw		2	PC
4	229463	A-1/4-S Silencer		1	PC
5		FP -3-1/4-B Clamping piece	Not available	1	PC
6	103652	V-3-1/4B Basic valve		1	PC
7	200932	B-14X1,5-N-NBR75 O-ring ISO3601	Lubricate with Molykote BR2 Plus during assembly	2	PC
8		FP - 3- 1/4 Switch jack	Not available	1	PC
9		FP -3-1/4 Tension spring	Not available separately, see position 998	1	PC
10		DIN 934-M4-6AU Hex nut	Not available separately, see position A	1	PC
11		DIN 553-M4X10-14H Threaded pin	Not available separately, see position A	1	PC
12		FP-3-1/4 Spring bearing	Not available separately, see position A	1	PC
13		8,2X18X7,5-1.0715+C Disc	Not available separately, see position A	1	PC
14		FP -3-1/4 Detent	Not available separately, see position A	1	PC
15		G-4,0 Grip ring	Not available separately, see position A	1	PC
16		FP -3-1/4 Compression spring	Not available separately, see position 998	1	PC
17		FP -3-1/4 Ring	Not available separately, see position A	2	PC
18		FP -3-1/4 VOLLST:LINKS Strap	Not available separately, see position A	1	PC
19		FP -3-1/4 Tension spring	Not available separately, see position 998	1	PC
20		KS-6 Clamping disc	Not available separately, see position A	2	PC
21		FP -3-1/4 VOLLST:RECHTS Strap	Not available separately, see position A	1	PC
22		M8X23-1.0715 Flat Head Screw	Not available separately, see position 998 Use locking compound LOCTITE-212/CASCO-187	2	PC
23	200531	DIN 906-R1/4-ST Plug screw	Use locking compound LOCTITE-212/CASCO-187	1	PC
24		DIN 553-M5X10-14H Threaded pin	Not available separately, see position A	1	PC
25		FP -3-1/4 Shaft	Not available separately, see position A Lubricate with MOLYKOTE-BR-2-PLUS during assembly	1	PC
26		DIN 922-M8X6X10-5.8 Flat Head Screw	Not available separately, see position A	2	PC
27			Not available	1	PC

Pos.	Part no.	Type	Note	Qty.	Unit
28	201953	FP -3-1/4 Pedal		1	PC
29		DIN 553-M4X8-14H Threaded pin	Not available separately, see position A	1	PC
30		FP -3-1/4-B Bolt	Not available separately, see position 998	1	PC
99 8	673703	FP-3-1/4-B / FP-5-1/4-B Assortment of springs		1	PC