

Features

- ESD – Designed to safely discharge static electricity and protect electronic components from electrostatic discharge events.
- Wheeled
- Height Adjustable
- Back Adjustable
- Synchro Mechanism
- Available in different sizes

RS PRO CLEANROOM ESD Comfort Chair

RS Stock No.: 0687610



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Our RS PRO CLEANROOM ESD Comfort chair is a professional seating solution designed for environments requiring strict electrostatic discharge (ESD) protection and exceptional cleanliness. Engineered for Cleanroom Class 5 conditions, it combines ergonomic comfort with high-performance materials to ensure safety, durability, and ease of use.

Product Features:

- ✓ **Ergonomically contoured seat and backrest** – provide optimal comfort and body support, even during long working hours
- ✓ **High-resilience foam** – ensures long-lasting cushioning and proper posture support
- ✓ **Five-star aluminum base** – offers strength, durability, and a sleek, professional appearance
- ✓ **Conductive rubber-coated castors** – protect floor surfaces and allow smooth mobility
- ✓ **ESD-safe dissipative vinyl upholstery** – easy to clean and designed for strict cleanliness standards
- ✓ **Synchro mechanism** – provides extensive adjustment options for optimal ergonomic support

An ideal solution for clean zones, laboratories, and production environments where electrostatic safety and contamination control are critical.

General Specifications

TOTAL HEIGHT (mm)	940-1145
TOTAL WIDTH (mm)	660
WEIGHT (kg)	12,5
MAX LOAD CAPACITY (kg)	120 (up to 200 kg with a special gas lift)
HEIGHT ADJUSTMENT RANGE (mm)	480-605mm
SEAT DIMENSIONS (mm)	455 x 430
BACKREST DIMENSIONS (mm)	500 x 420
ESD	YES
COLOUR	BLACK
MATERIAL	VINYL
FABRIC ABRASION RESISTANCE	UP TO 50,000 MARTINDALE'S CYCLES
BASE MATERIAL	ALUMINIUM
CASTORS	CONDUCTIVE, RUBBER-COATED TO PREVENT SCRATCHING
RESISTANCE GROUNDING (0hm)	$10^6 - 10^8$

Approvals

Chair compliance with standards	PN-EN IEC 61340-5-1:2025-02, PN-EN 1335-1:2004, PN-EN 1335-2:2009, PN-EN 1335-3:2009, PN-EN 1022:2007, PN-EN ISO 14644-1:2016-03
Fabric compliance with standards	PN-EN 1021-1:2014-12, PN-EN 1021-2:2014-12, BS 7176

Similar Products

Stock No.	Brand	Product Name
06876115	RS PRO	CLEANROOM ESD Comfort Chair (adjustment range: 570-750 mm)
06876125	RS PRO	CLEANROOM ESD Comfort Chair (adjustment range: 595-850 mm)
06876065	RS PRO	CLEANROOM ESD Basic Chair (adjustment range: 455-585 mm)
06876085	RS PRO	CLEANROOM ESD Basic Chair (adjustment range: 545-730 mm)
06876095	RS PRO	CLEANROOM ESD Basic Chair (adjustment range: 575-830 mm)

Accessories

Stock No.	Brand	Product Name
0687620	RS PRO	ESD castor, grey rubber tyre, diameter 50mm (**brake option available on request**)
XXX-XXX	RS PRO	ESD metal castor, diameter 50mm
0687621	RS PRO	ESD glides
0687599ESD	RS PRO	ESD footrest
XXX-XXX	RS PRO	ESD PU armrests
XXX-XXX	RS PRO	ESD armrests, black steel + antistatic PU cover
XXX-XXX	RS PRO	ESD armrests with height adjustment, black steel + antistatic PU covers