




Separation 3WA size 3, main busbar: top 3 or 4-pole, withdrawable H: 550 mm W: 1000 mm

| Model                                       |                              |
|---------------------------------------------|------------------------------|
| product brand name                          | SIVACON S4                   |
| product designation                         | Separation 3WA               |
| design of the surface                       | zinc plated                  |
| General technical data                      |                              |
| design                                      | assembly kit                 |
| suitability for use                         | for 3WA air circuit breakers |
| RAL color number                            | other                        |
| color                                       | miscellaneous                |
| Product details                             |                              |
| product component                           |                              |
| • cable entry                               | No                           |
| • lock                                      | No                           |
| Mechanical Design                           |                              |
| height                                      | 550 mm                       |
| width                                       | 1 000 mm                     |
| installation width for cabinet installation | 1 000 mm                     |
| shape of inner subdivisions                 |                              |
| • shape 2a                                  | No                           |
| • shape 2b                                  | No                           |
| • shape 3a                                  | No                           |
| • shape 3b                                  | No                           |
| • shape 4a                                  | No                           |
| • shape 4b                                  | No                           |
| material                                    | sheet-steel                  |
| Certificates                                |                              |
| reference code according to IEC 81346-2     | UC                           |
| Approvals Certificates                      |                              |
| General Product Approval                    | other                        |

[Miscellaneous](#)



[Miscellaneous](#)

| other                        | Environment                                       |
|------------------------------|---------------------------------------------------|
| <a href="#">Confirmation</a> | <a href="#">Environmental Con-<br/>firmations</a> |
|                              | <a href="#">Environmental Con-<br/>firmations</a> |

#### Further information

**Information on the packaging**

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8PQ5000-5BA11>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/8PQ5000-5BA11>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=8PQ5000-5BA11](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8PQ5000-5BA11)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>

---

last modified:

7/24/2023 

