



S51MC3H

3/8" Square Drive Standard and Deep Socket Set with Metric Hex Profile and 1/4" Bits - 51 pcs



PRODUCT DETAILS

- 12 hex sockets 3/8" standard 7400SM: 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 20, 22 mm
- 6 hex deep sockets 3/8" A7402SM: 10, 11, 13, 16, 17, 21 mm
- 1 ratchet 3/8" quick release 7750QR
- 1 spinner handle 1/4" 6956
- 2 extension bars 3/8" 7760: 75 mm, 150 mm
- 1 universal joint 3/8" 7766
- 1 bit holder 3/8" for 1/4" bits 7773A
- 1 bit holder 1/4" for 1/4" bits 6973A
- 59/PH: 5 bits 1/4" PH0, PH1, PH2, PH3, PH4
- 59S/: 3 bits 1/4" flat: SL4, SL5.5, SL8
- 59/PZ: 3 bits 1/4" PZ1, PZ2, PZ3
- 59/H: 6 bits 1/4" Hex, H3, H4, H5, H6, H8, H10
- 59/T: 8 bits 1/4" Torx, T8, T10, T15, T20, T25, T27, T30, T40
- 1 hex male adaptor to square male adaptor K6625-1/4
- Micro Matt finish
- High-performance 50BV30 alloy steel
- Spare case S51MC3H-BOX: high density polythene (HDPE)
- Standards: ISO 1174 and DIN 3120

PRODUCT ATTRIBUTES

Product				
S51MC3H	220 mm	220 mm	65 mm	1980 g

Follow the Fish!



SET CONTENT



**1/4" Square Drive Spinner Handle
150 mm
6956**



**3/8" Square Drive Socket with 10
mm Hex Profile
7400SM-10**



**3/8" Square Drive Socket with 11
mm Hex Profile
7400SM-11**



**3/8" Square Drive Socket with 12
mm Hex Profile
7400SM-12**



**3/8" Square Drive Socket with 13
mm Hex Profile
7400SM-13**



**3/8" Square Drive Socket with 14
mm Hex Profile
7400SM-14**



**3/8" Square Drive Socket with 15
mm Hex Profile
7400SM-15**



**3/8" Square Drive Socket with 16
mm Hex Profile
7400SM-16**



**3/8" Square Drive Socket with 17
mm Hex Profile
7400SM-17**



**3/8" Square Drive Socket with 18
mm Hex Profile
7400SM-18**



**3/8" Square Drive Socket with 19
mm Hex Profile
7400SM-19**



**3/8" Square Drive Socket with 20
mm Hex Profile
7400SM-20**



**3/8" Square Drive Socket with 22
mm Hex Profile
7400SM-22**



**3/8" Square Drive Universal Joint
51.5 mm
7766**

Follow the Fish!





1/4" Standard Screwdriver Bit for Philips PH4 Head Screws 25 mm - 10 Pcs/Plastic Box
59S/PH4



1/4" Square Drive Knurled Adaptor for 1/4" Hex Screwdriver Bit
6973A



1/4" Standard Screwdriver Bit for Slotted Head Screws 0.5 mm x 4 mm x 25 mm - 5 Pcs/Plastic Box
59S/0.5-4.0



1/4" Standard Screwdriver Bit for Slotted Head Screws 0.8 mm x 5.5 mm x 25 mm - 5 Pcs/Plastic Box
59S/0.8-5.5



1/4" Standard Screwdriver Bit for Slotted Head Screws 1.2 mm x 8 mm x 25 mm - 5 Pcs/Plastic Box
59S/1.2-8.0



1/4" Standard Screwdriver Bit for Philips PH0 Head Screws 25 mm - 10 Pcs/Plastic Box
59S/PH0



3/8" Square Drive Adaptors for 1/4" Hex Screwdriver Bits with Matte Finish
7773A



3/8" Pear Head Reversible Ratchet with 60 Teeth and 6° Action Angle 200 mm
7750QR



3/8" Square Drive Extension Bars 75 mm
7760-3



3/8" Square Drive Deep Socket with 16 mm Hex Profile
A7402SM-16



3/8" Square Drive Deep Socket with 13 mm Hex Profile
A7402SM-13



3/8" Square Drive Deep Socket with 17 mm Hex Profile
A7402SM-17



3/8" Square Drive Deep Socket with 10 mm Hex Profile
A7402SM-10



3/8" Square Drive Deep Socket with 11 mm Hex Profile
A7402SM-11

