

MeLE® QUIETER2Q

One of the best performance 4K palm-sized Fanless Mini Computer in the world

MeLE® Quieter2Q equipped with the 9th Intel® Celeron® Processor J4125 (2.0~2.7 GHz, 4 Cores, 4 Threads, supports 4M Intel Smart Cache), pre-installed 64-bit Windows® 10 Pro, dual HDMI 2.0 video output support 4K@60Hz, a home and business desktop computer. Ideal for home entertainment, Office, Education, Training center, Video Conference, Digital signage, IOT project etc.

MeLE® Quieter2Q built-in 8GB LPDDR4 2133MHz Memory and 128GB on-board Storage, support expanding the storage with a M.2 SATA/NvME 2280 SSD up to 4TB, a Micro SD card up to 1TB, four external SSD/Hard Drive up to 4TB.

MeLE® Quieter2Q supports 2.4G/5G dual-band Wi-Fi, Gigabit LAN port provides 1000Mbps transmission speed ensure a faster and stable internet connectivity. Bluetooth 4.2 can connect with wireless keyboard, mouse and other peripherals.

MeLE® Quieter2Q using Patented Passive Cooling Technology, it runs 0dB silently with high performance, no fan, no dust, no vibration, not only bring comfortable environment for users but also ensure its high performance for 7x24 hours working.

MeLE® Quieter2Q pre-installed 64-bit Windows 10 Pro which has a rich software ecology, efficient Office, also supports Linux operating system, such as Ubuntu 18.04, for server construction, software compilation and other needs. It supports Auto Power On, RTC Wake, Wake On LAN, PXE Boot, setting Boot order, etc.



Windows® 10 Pro
The faster, The better | Intel Inside® & Windows® 10

HDMI®
HIGH-DEFINITION MULTIMEDIA INTERFACE

HDMI 2.0 x2
Support 4K Ultra HD



QUIETER2Q

SYSTEM

Platform	Intel® Celeron® Processor J4125
Graphics	Intel® UHD Graphics 600
OS Support	Windows® 10 Pro
Languages Preloaded	English, Espanol, Português, Dutch, Deutsch, Polski, Chinese Simplified, русский, العربية, etc.
Memory	8GB LPDDR4
Storage	128GB eMMC
Expansion	1 x Micro-SD Card Slot
Internet Connectivity	802.11 ac WiFi (2.4G & 5G) & Bluetooth 4.2 100/1000Mbps Gigabit LAN Port
Video Output	2 x HDMI2.0 (3840*2160 4K@60 Hz)
Audio Output	2 x HDMI, 1 x 3.5mm Audio combo jack
USB Connection	4 x USB 3.0 Host
Warranty	One-year warranty and lifetime technical support, 7 Days and 24 Hours serving.
Power Supply	Input: AC 100-240V, Output: DC 12V=2A
Power Plugs	UL x 1 , UK x 1, GS x 1, SAA x 1
Dimensions	131 x 81 x 18.3mm
Weight	7.1oz / 203g
Security	Kensington Lock Slot



QUIETER2Q



MeLE TECHNOLOGIES (SHENZHEN) CO., LTD
Address: 3FW, MeLE Building, No.28 Cuijing Road,
Pingshan District, Shenzhen (518118) P.R.China

