

ADJUSTING SCREWDRIVERS


For all adjusting work which requires a ground blade

Adjusting screwdrivers with blade-tip made from special hard plastic

Material:

BERNSTEINIT with insert made from special plastic (German Federal Registered Pattern)

The BERNSTEINIT blade makes the screwdriver flexible, and the hard special plastic insert at the tip gives the blade exceptional torsional strength.



No.	overall length mm	blade length mm	blade Ø mm	blade width mm	weight g
1-151	85	40	3.0	3.0	3
1-152	85	40	4.0	4.0	3
1-153	175	130	3.0	2.0	4
1-154	175	130	4.0	3.0	5
1-155	175	130	5.0	3.5	6
1-156	175	130	5.0	4.0	6
1-157	225	180	4.0	3.0	6



1-150 **BERNSTEIN** Adjusting screwdrivers

7-piece set, as described above, clearly arranged in a plastic case
Weight: 75 g

Adjusting screwdrivers with metal inserts made from resilient hard bronze

For extremely firm cores or extremely small dimensions

Material: Handle made from BERNSTEINIT, blades made from special plastic with bronze tips



No.	overall length mm	blade length mm	blade Ø mm	bronze insert mm	weight g
1-301	200	155	2.7	1.4 x 0.5	4
1-302	200	155	2.7	2.0 x 0.5	4
1-303	200	155	2.7	2.5 x 0.5	4
1-304	200	155	2.7	1.7 x 0.7	4
1-305	125	80	2.4	1.1 x 0.5	3
1-306	125	80	2.4	1.7 x 0.7	3
1-307	125	80	2.4	2.0 x 0.5	3



1-300 **BERNSTEIN** Adjusting screwdrivers,

7-piece set, as described above, clearly arranged in a plastic case
Weight: 70 g

1-180 **BERNSTEIN** Adjusting tools

7-piece set in a plastic case
Weight: 70 g



No.	Description of individual tools
	Adjusting screwdrivers made from BERNSTEINIT with hard special plastic insert
1-151	Overall length 85 mm, blade 40 x 3.0 mm
1-152	Overall length 85 mm, blade 40 x 4.0 mm
1-153	Overall length 175 mm, blade 130 x 2.0 mm
1-155	Overall length 175 mm, blade 130 x 3.5 mm
1-181	Double-ended adjusting key made from BERNSTEINIT with hard special plastic inserts, overall length 180 mm, one end hexagonal 1.85 mm A/F, other end square 1.5 mm A/F
1-182	Double-ended adjusting key made from BERNSTEINIT with hard special plastic inserts, overall length 180 mm, one end hexagonal 2.6 mm A/F, other end square 3.0 mm A/F
1-306	Adjusting screwdriver made from special plastic, overall length 125 mm, blade 80 x 2.4 mm, with bronze insert 1.7 x 0.7 mm